

Actuator

704.101.018



<https://eao.com/p/704.101.018>

Your product:



704.101.018 Actuator

FRONT

Front dimension:	Ø 35 mm
Front bezel colour:	Nature
Front bezel material:	Aluminium

MOUNTING

Mounting cut-out:	Ø 30.5 mm
Design:	flush

OPERATING-/INDICATION PART

Lever colour:	Black
Lever shape:	long
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching positions:	2 positions
Weight:	0.056 kg
Switching action:	Rest - Maintained
Mechanical lifetime:	≤2.5 Mio. cycles of operation
Switching angle:	90° right / -45° ... +45°


AMBIENT CONDITION

Operating temperature:	– 40 °C ... + 55 °C
IP Protection:	IP65 front side
Storage temperature:	– 40 °C ... + 85 °C

OTHER

Hints:	Max. 3 switching elements can be clipped on
Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, non illuminative, Black, long, Nature, Aluminium, anodised, Rest - Maintained
max. number of switching elements:	3

Dimension drawings:




A = Screw terminal


Wiring diagrams:



Switching positions:



Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm