



深圳市兴华鑫电子科技有限公司
Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer): _____
客戶料號 (Customer P/N): _____
興華鑫型號 (Supplier P/N): XHXDZ-4230 腔体-8 欧 2 瓦
產品名稱 (Description): 喇叭 (Speaker)
產品規格 (Specification): _____

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)	
	審核	制作
	唐国兴	田鑫
	日期: 2024 年 06 月 18 日 版次: A	

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层
TEL: 0755-27892904
E-mail: jacky.tang@jsxhxdz.com
Http: www.jsxhxdz.com

深圳市兴华鑫电子科技有限公司

Model No.	XHXDZ-4230 腔体-8 欧 2 瓦	Date	2024-06-18	Page No.	1 / 5
-----------	-----------------------	------	------------	----------	-------

產品規格內容 (SPECIFICATION)

1.使用範圍 (Scope)

此份規格書是針對多媒體產品內，所使用的微型揚聲器單體所提出的報告。

This specification covers our product of miniature speaker unit for multimedia product.

2.标准测试条件(Test condition)

一般规格试验状态（特殊要求除外）：常温 5~35℃，常湿 45%~85%，气压 860~1060hPa.

判定上有疑问时，试验状态为：温度 20±2℃，相对湿度 60%~70%，气压 860~1060 hPa.

The test conditions unless otherwise specified should be normal temperature 5 to 35 ℃,Normal humidity 45 to 85% and normal atmospheric pressure 860 to 1060 hPa,However,if there arises a doubt in judgment,the test conditions shall beas follows:

Temperature 20±2℃

Humidity 60%~70%

Atmosphere 860~1060 hPa

3.電聲特性 (ELECTRO-ACOUSTIC CHARACTERISTICS)

3.1 額定阻抗(Rated Impedance):

8Ω ± 15% (AT 1.6K Hz ,4.0 Vrms)

3.2 額定輸入功率(Rated Input Power)

2Watt (At 4.0Vrms white noise 96 Hours)

3.3 最大輸入功率(Max. Input Power)

2.2 Watt

3.4 最低共振頻率(Resonant Frequency)

1500 Hz ± 20%

3.5 輸出音壓(Output S.P.L)

98 ± 3dB (1.0 Watt , 0.1 Meter. Average at 1.5K,2.0K,2.5K,3.0K Hz)

3.6 實效頻率範圍(Frequency Range)

Fo ~ 20KHz (By Output S.P.L. -10dB)

3.7 失真率(Distortion)

Less than 5% (At 1.6KHz , 4.0Vrms)

3.8 工作溫度(Operating Temperature)

-25℃ ~ +50℃

3.9 儲存溫度(Storage temperature)

-25℃ ~ +55℃

制 定

审 核

核 准

文 件 编 号


唐国兴

產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-4230 腔体-8 欧 2 瓦	Date	2024-06-18	Page No.	2 / 5
-----------	-----------------------	------	------------	----------	-------

4.可靠性測試 (Reliability Test)

4.1 高低溫差循環測試(Temperature Cycling Test)



A	Low Temperature (-25°C±3°C)
B	High Temperature (+55°C±3°C)
C	Number of Cycle (3 Cycles)
D	Duration of Exposure 1 Hours, at Each Temperature Extremes
E	Duration of Recovery 1 Hours

4.2 抗濕度試驗(Humidity Test)

A	相對濕度(Relative Humidity)	90-95% at + 40°C ± 3°C
B	測試時間(Durations)	96 Hours
C	恢復時間(Durations of recovery)	6 Hours

4.3 連續負載測試(Load Test)

White Noise Without Weighted Filter 4.0Volts.(RMS) 96 Hrs.

4.4 跌落試驗(Drop Test)

75 cm Free Falling On Concrete Floor, 10 Times.

4.5 異常音測試(Buzzes & Rattles)

Sine wave between at 4.0Vrms / 50~5000Hz



4.6 極性測試(Polarity test)

Diaphragm Shall Move Forward When Apply a Positive DC. Current to the “+”or “Marked” Terminal.

產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-4230 腔体-8 欧 2 瓦	Date	2024-06-18	Page No.	3 / 5
-----------	-----------------------	------	------------	----------	-------


5.測量方式 (Measurement Method)




產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-4230 腔体-8 欧 2 瓦	Date	2024-04-10	Page No.	4/5
-----------	-----------------------	------	------------	----------	-----

6. 頻率響應曲線圖(Frequency Response Curve)



7. 阻抗曲線圖(Impedance Curve)



產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-4230 腔体-8 欧 2 瓦	Date	2024-06-18	Page No.	5 / 5
-----------	-----------------------	------	------------	----------	-------

8. 喇叭外觀描述

(Unit:mm tolerance:±0.3)

