

Coaxial Bandpass Filter

ZABP-450-S+

50Ω 400 to 510 MHz

The Big Deal

- High rejection
- Good VSWR
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: UU1842

Product Overview

ZABP-450-S+ is a 50Ω bandpass filter with a rugged connectorized package covering the passband of 400 to 510 MHz. The bandpass filter offers good matching within the passband and provides high rejection. This filter has miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
High rejection	ZABP-450-S+ has sharper transition and rejects spurious signals in the stopband.
Good VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω 400 to 510 MHz

ZABP-450-S+



Generic photo used for illustration purposes only

CASE STYLE: UU1842

Connectors Model
SMA-MF ZABP-450-S+


Features

- High rejection
- Good VSWR, 1.25:1 @ passband
- Connectorized package


Applications

- Military and avionics
- Receiver / transmitters
- Harmonic rejection
- Test equipment

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	450	-	MHz
	Insertion Loss	F1-F2	-	1.0	2	dB
	VSWR	F1-F2	-	1.25	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	40	50	-	dB
		F3-F4	20	30	-	dB
	VSWR	DC-F4	-	18	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	20	35	-	dB
		F6-F7	-	50	-	dB
	VSWR	F5-F7	-	18	-	:1





Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W max.

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	83.94	6881.00	400	6.21
50	53.22	2353.20	405	5.96
150	52.15	239.30	410	5.76
310	29.67	36.53	415	5.58
320	20.49	29.37	420	5.45
330	13.93	19.92	425	5.33
342	7.94	9.69	430	5.24
355	3.72	4.06	435	5.16
400	0.85	1.19	440	5.11
450	0.79	1.23	445	5.07
455	0.78	1.20	450	5.04
510	0.90	1.25	455	5.03
590	3.19	2.42	460	5.03
630	14.76	11.44	465	5.02
645	20.10	16.08	470	5.04
675	30.28	23.07	475	5.04
700	38.51	26.37	480	5.06
760	70.06	29.19	490	5.11
1000	53.97	32.23	500	5.17
1200	49.91	33.45	510	5.25



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

Outline Drawing



Outline Dimensions (^{inch}_{mm})

A	B	C	D	E
2.300	2.250	.750	2.175	2.125
58.42	57.15	19.05	55.25	53.98

F	G	H	J	wt.
.125	.125	.312	1.125	grams
3.18	3.18	7.93	28.58	124

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp