



600H005 Connector holding tool, plug and receptacle

MIL-DTL-38999 Series III type



Dimensions					
Shell Size	A Dia Max	B Dia Max	C Dim Max	Recommended Torque (±5 inch-pounds)	
				Metal	Composite
09	.577 (14.7)	.438 (11.1)	1.031 (26.2)	60	35
11	.709 (18.0)	.566 (14.4)		80	35
13	.829 (21.1)	.678 (17.2)		110	40
15	.954 (24.2)	.803 (20.4)		120	40
17	1.107 (28.1)	.928 (23.6)		120	40
19	1.190 (30.2)	1.033 (26.2)		120	40
21	1.315 (33.4)	1.158 (29.4)		140	80
23	1.440 (36.6)	1.283 (32.6)		140	80
25	1.565 (39.8)	1.408 (35.8)		140	80
25L	1.565 (39.8)	1.408 (35.8)		140	80

NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.
4. Composite values apply when using Glenair 600-091 and 600-007 tools.