




| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | D2  | REVISED PER ECR-18-014346 | 13SEP2018 | JH  | PKS  |



|                                        |                                                                                                                                             |                                                   |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|
| -                                      | -                                                                                                                                           | -                                                 |
| -                                      | -                                                                                                                                           | -                                                 |
| -                                      | -                                                                                                                                           | -                                                 |
| -                                      | -                                                                                                                                           | -                                                 |
| Pre-Tin Plate over Copper Underplate   | -                                                                                                                                           | 4-1601112-2                                       |
| Pre-Tin Plate over Copper Underplate   | 131-187-014                                                                                                                                 | 1601112-2                                         |
| FINISH                                 | REFERENCE<br>PART NUMBER                                                                                                                    | TYCO<br>PART NUMBER                               |
| THIS DRAWING IS A CONTROLLED DOCUMENT. | DWN<br>J.WELLER<br>11JAN2002<br>CHK<br>M.FEHER<br>11JAN2002<br>APVD<br>K.RANDOLPH<br>11JAN2002                                              | NAME<br><b>TE</b> TE Connectivity Ltd.            |
| DIMENSIONS:<br>INCHES                  | TOLERANCES, UNLESS<br>OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± .01[0.25]<br>3 PLC ± .005[0.13]<br>4 PLC ± -<br>ANGLES ± 2° | PRODUCT SPEC<br>108-2085<br>APPLICATION SPEC<br>3 |
| MATERIAL<br>BRASS, 1/2 HARD            | FINISH<br>SEE TABLE                                                                                                                         | WEIGHT<br>0.000000<br>CUSTOMER DRAWING            |
| SIZE<br>A2                             |                                                                                                                                             | CAGE CODE<br>00779                                |
| DRAWING NO<br>C-1601112                |                                                                                                                                             | RESTRICTED TO<br>-                                |
| SCALE<br>1:6                           |                                                                                                                                             | SHEET<br>1 OF 1                                   |
|                                        |                                                                                                                                             | REV<br>D2                                         |