







LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
				P		REVISED PER ECO-11-004835		11MAR11	RK	HMR

- 1 MATERIAL: ZINC ALLOY DIE CASTING.
- 2 SURFACE FINISH: CHROMATE CONVERSION COATING.
(ROHS COMPATIBLE).



P/N 223986-2 AS SHOWN



FOOT PRINT

8	315°	5223986-8
7	270°	5223986-7
6	225°	5223986-6
5	180°	5223986-5
4	135°	5223986-4
3	90°	5223986-3
2	45°	5223986-2
1	0°	5223986-1
KEYING POSN		DIM A
PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	OSAPROS	TE Connectivity	
DIMENSIONS:		CHK R. PATTERSON	OSAPROS	NAME	
mm		APVD R. PATTERSON	OSAPROS	MODULE, FEMALE, UNIVERSAL POWER MODULE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	APPLICATION SPEC	RESTRICTED TO	
0 PLC ± -		SIZE	CAGE CODE	DRAWING NO	
1 PLC ± -		WEIGHT	—	—	
2 PLC ± 0.13		A1 00779 C=5223986			
3 PLC ± -		CUSTOMER DRAWING			
4 PLC ± -		SCALE 4:1			
ANGLES ± -		SHEET 1 of 1			
FINISH		REV P			