







PARTS LIST

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040044	D16OAT14
2	-	-	NO LAMP
3	1	F050204	5000204 TRANSPARENT RED LENS RECTANGULAR CONCAVE

4PDT
CONTACT CONFIGURATION

PANEL MOUNTING



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC, 8A @ 125 VAC
6A @ 24 VDC
5. ELECTRIC LIFE: 50,000 CYCLES
6. INSULATION RESISTANCE: 1,000 M Ω MIN.
7. PANEL THICKNESS: 0.5 - 5.0 mm
8. SEAL RATING: IP40
9. OPERATING TEMP.: -25°C to 55°C
- ▲ 10. LAMP VOLTAGE: NO LAMP
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/05/EC (ROHS) COMPLIANT.
- ▲ 13. TRAVEL: 3.0mm FULL - MOMENTARY



A	22032	RELEASED FOR PRODUCTION	10/29/15	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16OAT140RED

SCALE
3:2DATE
10/29/2015DR
MWDWG
XF0904PREV
A