



- 1MAGNET WIRE: #18 - 34 AWG, 1.02[.040]-0.16[.006] DIA. COPPER.
OTHER SIZES MAY BE ACCOMMODATED,CONSULT TYCO ELECTRONICS
FOR APPROVAL.
- 2POCKET RECOMMENDATION:
#1601425 EXCEPT ONLY 7.87[.310] DEEP
- 3TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
APPLICATION SPECIFICATION 114-13166 FIGURE 7.
- 4BACK SIDE WITH IDC BEAMS PROTRUSION



OBSOLETE	Pre Tin Plate	131-162-002	6-1601090-2
	Pre Tin Plate	031-161-002	4-1601090-2
	Pre Tin Plate	131-162-002	2-1601090-2
	Pre Tin Plate	131-161-002	1601090-2
FINISH		REFERENCE PART NUMBER	TE PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002 PRODUCT SPEC 108-2085 APPLICATION SPEC 3	NAME STANDARD RANGE WIRE TO 2.0 x 0.51 TAB SIAMEZE TERMINAL
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°	SIZE A2	
MATERIAL BRASS, SPRING HARD	FINISH SEE TABLE	WEIGHT -	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1
		REV F	RESTRICTED TO -