

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

LOC

DIST

REVISIONS

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD

O

TRANSFERED TO TYCO FORMAT

16SEP02




MF

EH

1 CRIMPBAND MATERIAL PROVIDED IN CONTINUOUS STRIP.


2 REFERENCE DESCRIPTIVE PART NUMBER L125D20TCRS.

3 BLANK LENGTH DETERMINED BY 125 TOOLSET.



PARTIAL FORMED VIEW (REF)
FORMED BY APPLICATION TOOLING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESMATERIAL
UNS G10100 COLD
ROLL STEELTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FINISH
TINDWN 16SEP2002
MICHAEL S. FEHERCHK 16SEP2002
EDWARD HOWARDAPVD 16SEP2002
EDWARD HOWARD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

CRIMPBAND, RTM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1601733

SCALE 1:1

SHEET 1 OF 1

REV 0

1601733-1

PART NUMBER