








△ DIMENSION

Dim A	NX5.00
Dim B	NX5.00+1.40

N=Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.35



SIGN	DATE	DESCRIPTION	APPROVER
△	10/17/13	Add is cULus ///add the view THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	Da cheng

Material

- Item (a) Terminal (Body): Thermoplastic (UL94V-0)
- Item (b) Terminal (Lever): Thermoplastic (UL94V-0)
- Item (c) Spring clamp : Stainless Steel
- Item (d) Female Contact : PhBz(CuSn), Tin plated
- Item (e) Terminal (Cover): Thermoplastic (UL94V-0)

△ Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Solid wire(AWG): 14-26
- Stranded wire(AWG): 14-26
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Size of the PCB: 1.6±0.2mm
- Operating temperature: -40°C to +115°C

△ Safety Approval:

△ Critical dimension:



ND xx 70 x 0 xxxx G

- △ No. of poles
- 02 2 poles
 - 03 3 poles
 -
 - 24 24 poles

- △ Color
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors

△ RoHs compliant
(lead<4%)
In copper Alloy

0000:"@Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ND 5.0 Series							
PART NO.	NDxx70x0xxxxG				DWG NO.	8ND0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Dacheng 2013.10.21	Dacheng 2013.10.21				UNIT: mm	X. ±0.5
		SHEET: 01/01	SCALE: NONE				X.X ±0.3	
					REV.: C	X.XX ±0.1	X° ±1°	