

D

C

B

A






D

C


B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL DRAWING	18OCT2021	TL	HL



RECOMMEND PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN
TOLERANCE ±0.05



1 MATERIAL:
CONTACT: COPPER ALLOY.
HOUSING: GLASS-FILLED POLYESTER.

2 GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION
PIN: 0.5µm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.

2/3	2391870-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 27MAY2021	TE Connectivity Ltd.	
		CHK ALEX XU 27MAY2021		
DIMENSIONS: mm		APVD HOPE LU 27MAY2021	NAME MALE ASSEMBLY, Z-PACK 2mm HM, 110P TYPE A EON	
		PRODUCT SPEC 108-19082	SIZE A1	
		APPLICATION SPEC 114-160149		
MATERIAL 1		WEIGHT 0	RESTRICTED TO —	
FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 4:1
		SHEET 1 OF 1		REV A