

Customer Information Sheet

DRAWING No.: M22-543XX05


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



ORDER CODE:

M22-543XX05

No. OF CONTACTS PER ROW:
03 TO 15, 20

**Active
products:**

**M22-5430405
M22-5430505
M22-5432005**

SPECIFICATION:

MATERIAL:

MOULDING = PA9T, UL94V-0, BLACK

CONTACT = BRASS

FINISH:

CONTACT = GOLD FLASH OVER NICKEL

ELECTRICAL:

CURRENT RATING = 1.5A

CONTACT RESISTANCE = $20\text{m}\Omega$ MAX

INSULATION RESISTANCE = $1000\text{M}\Omega$ MIN


DIELECTRIC STRENGTH = 500V AC/DC MINUTE

ENVIRONMENTAL:


TEMPERATURE RANGE = -40°C TO $+105^{\circ}\text{C}$

PACKING: BOX

FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C018XX (LATEST ISSUE)




OBSOLETE
All other size/finish
combinations not
listed above



NOTES:

1. DIMENSION TOLERANCES = ± 0.25 UNLESS
OTHERWISE STATED.



MSP	10	09.08.17	20547
NAME	ISS.	DATE	C/NOTE
APPROVED:		M.PERREN	
CHECKED:		S.BENNETT	
DRAWN:		J. EVANS	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^{\circ}$
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

2.00mm PITCH DIL HORIZONTAL
SMT PIN HEADER ASSEMBLY

DRAWING NUMBER:

M22-543XX05

SHT
2 OF 2