


Coaxial PCB Connector
85_MCX-S50-0-25/111_N

Description

Right angle PCB jack

Interface Standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type surface mount
Weight 0.0016 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012850
Mounting hole DOU-00012852

Ordering Information

Bulk 100 pcs package 85_MCX-S50-0-25/111_NH
Tape and Reel package 85_MCX-S50-0-25/111_NM