


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
Z		REVISED PER ECO-08-012630	22MAY08	HMR	GS
Z1		REVISED PER ECO-09-020935	09SEP09	KK	AEG
AA		REVISED PER ECO-17-011042	02AUG2017	RS	MZ



- 1 0.76µm[.000030] MIN GOLD, INTERNALLY, FOR A LENGTH OF 5.08[.200] FROM MATING END WITH GOLD FLASH ON REMAINDER, ALL OVER 0.76µm[.000030] MIN NICKEL.
- 2 POSTS ARE SEMI-AUTOMATICALLY WIREABLE AND WILL ACCOMODATE (SEE TABLE) TERMINATIONS.
- 3 #24 AWG MAX WIRE TO BE USED WITH THIS CONNECTOR.
- 4 FOR PANEL CUTOUT SEE AMP CUSTOMER DWG 201692.
- 5 2.54µm[.000100] MIN TIN-LEAD OVER 1.27µm[.000050] MIN NICKEL.
- 6 2.54µm[.000100] MIN TIN OVER 1.27µm[.000050] MIN NICKEL.
- 7 GOLD FLASH OVER .000050 MIN NICKEL.
- 8 PRELIMINARY NOT FOR PRODUCTION.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

9	OBSOLETE	7	6.63 [.261]	1	8 1-205720-1
	OBSOLETE	6	16.74 [.659]	3	1-205720-0
		6	6.63 [.261]	1	205720-9
		5	16.74 [.659]	3	205720-2
		5	6.63 [.261]	1	205720-1
	POST FINISH	A	NO OF TERM	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. REIFSNYDER CHK R. STONE APVD M. MCALONIS	14 FEB 96 22 FEB 96 22 FEB 96	TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	SOCKET ASSY, AUTOWIRE, 104 POSN, W/CENTER FASTENER STANDARD M SERIES	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT	A1	00779	©=205720
CUSTOMER DRAWING			SCALE	4:1	SHEET 1 OF 1
			REV AA		