



Technical drawing of a plate with 10 rows of holes. The plate has a width of 34.76 and a height of 5.08. The holes are arranged in 10 rows, numbered 1 to 10 from right to left. The distance between the center of the first row (row 1) and the center of the last row (row 10) is 22.86, calculated as 9×2.54 . The distance from the left edge of the plate to the center of the first row is 2.54. The distance from the right edge of the plate to the center of the last row is 2.54. The hole diameter is $\varnothing 2.8^{+0.1}$. The hole spacing is 1 ± 0.1 . The hole position tolerance is $\varnothing 0.05$. The text "alle Löcher / all holes" is present.

Consider protection memo from DIN 34	Information:				Tolerances		 All Dimensions in mm	Scale	2:1	
	All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.			Designation		
								Federleiste C/3, 30 Löt <i>Fem. Connector C/3, 30 Solder</i>		
								254320		
	Index		Date		H:00061240.SZA		STVC/3			