



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECO-21-006944	12OCT2021	RK	MZ



DETAIL A



DETAIL B

- 1 WILL ACCEPT (8) MULTIMATE PINS AND (5) TYPE XII MALE CONTACTS.
- 2 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 3 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 4 MAX WIRE INSULATION DIAMETERS:
MULTIMATE: 3.43[.135] MAX DIA.
TYPE XII: 5.59[.220] MAX DIA.
- 5 THIS RECEPTACLE MATES WITH PLUG ASSEMBLY 211824-1.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

6 OBSOLETE	YES	A	211825-3
	NO	B	211825-2
	NO	A	211825-1
PERIPHERAL SEAL		SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER 05/26/94	TE Connectivity	
		CHK R. STONE 6-23-94		
DIMENSIONS: mm[INCHES]		APVD A. FRANTUM 7-13-94	NAME RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC	
		PRODUCT SPEC 108-10024	SIZE A1	
		APPLICATION SPEC		
MATERIAL HOUSING: NYLON, BLACK		WEIGHT -	RESTRICTED TO -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV G	