


# Actuator

704.042.5



<https://eao.com/p/704.042.5>

Your product:

---



## 704.042.5 Actuator

### FRONT

Front dimension:	Ø 29 mm
Front bezel material:	Aluminium
Front bezel colour:	Nature
Front form:	round

### MOUNTING

Design:	raised
---------	--------

### OPERATING-/INDICATION PART

Lens colour:	Green
Lens material:	Plastic
Lens shape:	flush
Lens illumination:	non illuminative
Lens optics:	transparent

### ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

### MECHANICAL CHARACTERISTIC

Mechanical lifetime:	≤3 Mio. cycles of operation
Operating force:	8 N
Operating Travel:	ca. 5.8 mm ± 0.2 mm

**Weight:** 0.04 kg

**Switching action:** Maintained

### AMBIENT CONDITION

**Storage temperature:** – 40 °C ... + 85 °C

**IP Protection:** IP65 front side

**Operating temperature:** – 40 °C ... + 55 °C

### OTHER

**Housing material:** Plastic


**Hints:** Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on

**Short Description:** Actuator, Ø 29 mm, flush, non illuminative, Green, Plastic, transparent, round, Nature, Aluminium, anodised, Maintained


**max. number of switching elements:** 3

**Housing colour:** Grey

**Wiring diagrams:**




**Mounting cut-outs:**



A = Screw terminal  
B = Push-in terminal (PIT)  
C = Plug-in terminal 6.3 mm x 0.8 mm  
D = Double plug-in terminal 6.3 mm x 0.8 mm

**Dimension drawings:**



A = Screw terminal