

LOC	DIST	REVISIONS						
A1	-	P	LTR	DESCRIPTION		DATE	DWN	APVD
			E6	ECR-21-118726		27OCT2021	PJ	FL
			E7	ECR-21-121619		06DEC2021	PJ	FL
			E8	ECR-23-183576		08SEP2023	DC	FL
			E9	REVISED PER ECR-24-199015		11MAR2024	AK	FL

REMARKS/Bemerkungen

- 1

CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in Prod. Spec. 108-18049, Punkt 3.3.2
- 2

CONTACT CAVITY NO.
Kontaktkammernummerierung
- 3

MATING STOP
Tiefenanschlag
- 4

AREA FOR TE LOGO ACC: TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36
- 5

POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
- 6

KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
- 6a

KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
- 7

LOCKING LATCH
Rasthaken
- 8

TE PART NO (PN)
TE Bestell Nr. (PN)
- 9

DESIGN OF THE HOUSINGS ACC: TO RAST 5 STANDARD
Gehäuseausführung gemäß RAST 5 Vorgabe
- 10

GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe
- 11

PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton
- 12

DIMENSION A, B C AND D SEE SHEET 2 OF 3
- 13

MATERIAL CORRESPONDS TO THE REQUIRMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahttest 750° ohne Flamme)
- 14





OPTIONAL RATIO NUMBER OF THE KEYING VERSION, MOLDED OR INKJET PRINTED. SEE SHEET 2
Optionale Kodierungskennnummer, mit Tintenstrahldrucker aufgebracht oder spritzgegossen, siehe Blatt 2
- 15

PRELIMINARY- NOT RELEASED FOR PRODUCTION
- 16

ONLY FOR 9-1241961-7, DIMENSION 3.2 -0.2
- 17

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL
- 18


ALLOWED 25±0.2 FOR P/Ns X-2364739-X.



SECTION A-A / Schnitt A-A

SECTION B-B / Schnitt B-B

5 POSITION
STD. TIMER MARK-II HOUSING



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: Kishor M.	18-10-07	 TE Connectivity		
DIMENSIONS:		CHK: K.Munz	18-10-07			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: T.K. Klenner	18-10-07	NAME: STANDARD TIMER HSG. RAST 5 MARK II		
		PRODUCT SPEC.		Standard Timer Gehäuse RAST 5 Mark II		
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±° FINISH -	APPLICATION SPEC.		SIZE: 00779		
		WEIGHT: -		RESTRICTED TO: -		
MATERIAL: SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		Customer Drawing		SCALE: 5:1		
				SHEET: 1 OF 4		
				REV: E		

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

ONLY 5-1241961-7, 1-1241961-9, 7-1241961-7, 2345753-1, 2-2178571-3

3

2.8

3.7

1.5

ALL OTHER DIMENSIONS SEE SHEET 1 OF 3

KEY LAYOUT DESCRIPTION

“X”

3

7

5

VIEW “X”

YYY

4

6a

6

6

7

5

5

6a

8

X-XXXXXX-X

DIFFERENT CAVITY GEOMETRY AND LOCKING LATCH OVERHANG (OPTIONAL)

FOR 2 POS. AND 3 POS.

B

1.5.o.2

9

1.5.o.2

(4.2)

(3.45)

SECTION B-B/Schnitt B-B

ALL OTHER DIMENSIONS SEE SHEET 1 OF 3

Alle anderen Masse siehe Seite 1 von 3

SPECIAL MATERIAL: UL94 V0

2345753-1

3

6

1

15

10

PA66

NATURAL

C

SPECIAL MATERIAL

1955507-4

4

6

1

20

15

PA66

NATURAL

1

9-1955506-2

2

10

5

UL 94 V0

NATURAL

1

15

16

6-1241961-7

3

4

0.5

15

10

PA 6 UL94V-2

NATURAL

1

4-1241961-7

3

15

10

PA 6 UL94V-2

NATURAL

A

3-1241961-7

3

15

10

PA 6 UL94V-2

NATURAL

A

1-1955422-7

3

15

10

PA 66 UNFILLED UL94 V0

NATURAL

A

5-1955422-7

3

15

10

PA 66 UNFILLED UL94 V0

NATURAL

A

4-1955422-3

2

10

5

PA 66 UNFILLED UL94 V0

NATURAL

A

2-1241817-3

3

4 or 6

0.5 or 1

15

10

PA 66 UL94 V-2

Green

E

0-1955422-6

3

15

10

PA 66 UNFILLED UL94 V0

NATURAL

A

8-1241961-8

3

15

10

PA 6 UL94V-2

natural

C

0-1241961-8

3

15

10

PA 6 UL94V-2

natural

A

8-1241961-3

2

10

5

PA 6 UL94V-2

NATURAL

C

3-1241961-1

2

10

5

PA 66 UNFILLED UL94 V0

NATURAL

C

0-1955422-1

2

10

5

PA 66 UNFILLED UL94 V0

NATURAL

A

PART NO

POS

DIM C

DIM D

DIM A

DIM B

MATERIAL

COLOUR Farbe

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±0.2

±0.2

±0.2

±

±*

MATERIAL

SEE TABLES, SHEETS PAGE 2 AND 3 OF 4

18-10-07

18-10-07

18-10-07

Customer Drawing

SCALE 5:1

SHEET 2 OF 4

REV E9

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±0.2

±0.2

±0.2

±

±*

MATERIAL

SEE TABLES, SHEETS PAGE 2 AND 3 OF 4

18-10-07

18-10-07

18-10-07

Customer Drawing

SCALE 5:1

SHEET 2 OF 4

REV E9

LOC

DIST

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET-01

0-1241959-5

5

25

20

PA 6 UL94V-2

Natural/natur

B

4-1241959-4

4

20

15

PA 6 UL94V-2

Natural/natur

A

2-1241959-4

4

20

15

PA 6 UL94V-2

Natural/natur

B

0-1241959-4

4

20

15

PA 6 UL94V-2

Natural/natur

B

2-1241817-5

5

25

20

PA 6.6 UL94V-2

Natural/natur

C

0-1241817-5

5

25

20

PA 6.6 UL94V-2

Black/schwarz

C

3-1241817-4

4

20

15

PA 6.6 UL94V-2

Violet/violett

C

2-1241817-4

4

20

15

PA 6.6 UL94V-2

Grey/grau

C

0-1241817-4

4

20

15

PA 6.6 UL94V-2

Natural/natur

C

2-1241983-2

2

10

5

PA 6 UL94V-2

Green/grün

C

1-1241983-2

2

10

5

PA 6 UL94V-2

Violet/violett

C

0-1241983-2

2

10

5

PA 6 UL94V-2

TARGET RAL 4001

C

8-1241983-2

2

10

5

PA 6 UL94V-2

Yellow/gelb

C

5-1241983-3

2

10

5

PA 6 UL94V-2

Black/schwarz

C

6-1241983-2

2

10

5

PA 6 UL94V-2

Blue/blau

C

0-1241983-2

2

10

5

PA 6 UL94V-2

Red/rot

C

6-1241961-7

3

15

10

PA 6 UL94V-2

Natural/natur

C

9-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

6-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

5-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

4-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

7-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

1-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

3-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

2-1241961-8

3

15

10

PA 6 UL94V-2

Natural/natur

C

2-1241961-7

3

15

10

PA 6 UL94V-2

Natural/natur

C

9-1241961-9

3

15

10

PA 6 UL94V-2

Natural/natur

C

1-1241961-7

3

15

10

PA 6 UL94V-2

Natural/natur

C

0-1241961-6

3

15

10

PA 6 UL94V-2

Natural/natur

C

3-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

2-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

5-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

4-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

7-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

7-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

6-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

3-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

5-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

6-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

0-1241961-3

3

15

10

PA 6 UL94V-2

Natural/natur

C

8-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

9-1241961-2

3

15

10

PA 6 UL94V-2

Natural/natur

C

0-1241961-1

3

15

10

PA 6 UL94V-2

Natural/natur

C

9-969484-9

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-8

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-8

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-8

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

9-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

8-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

7-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

6-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

5-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

3-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

1-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-7

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

9-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

8-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

7-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

6-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

5-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

3-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

1-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-6

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

9-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

8-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

7-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

6-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

5-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

3-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

1-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-3

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

9-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

8-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

7-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

6-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

5-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

3-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

1-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-2

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

9-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

8-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

7-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

6-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

5-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

4-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

3-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

2-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

1-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

0-969484-1

3

15

10

PA 6.6 UL94V-2

Yellow/gelb

H

PART NO

POS.

DIM C

DIM D

DIM A

DIM B

MATERIAL

COLOUR

REV

TE

TE Connectivity

STANDARD TIMER HSG. RAST 5 MARK II

Standard Timer Gehäuse RAST 5 Mark II

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A 1

00779

©=1241961

-

4805 (3/11)

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
				SEE SHEET-01				

SPECIAL VERSION: UL94 V0 & GWPT 750°C NF								
2364739-5	5	4	0.5	25	20	PA66 13 17	BLUE	C
2364739-4	4			20	15		BLUE	C
1-2364739-3	3			15	10		BLUE	C
2364739-3				15	10		BLUE	C
1-2364739-2	2			10	5		BLUE	C
2364739-2				10	5		BLUE	C
3-2364739-2	2			10	5		BLUE	C
2-2364739-2				10	5		BLUE	C

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350								
5-1241961-7	3	6	1	15	10	PA6613	NATURAL	A
1-1241961-9	3			15	10		NATURAL	A
7-1241961-7	3			15	10		NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
152322164-1	4	4	0.5	20	15	PA6613	NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF								
6-2178575-7	3	4	0.5	15	10	PA6 GF1513	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
153-2178412-7	3	6	1	15	10	PA66 UL94 V0 & GWT 750 NF13	NATURAL	1
154-2178412-7	3			15	10		NATURAL	1
158-2178412-2	2			10	5		NATURAL	1

UL94 V0 & GWT 750 NF								
2322917-4	4	4	0.5	20	15	PA66 UL94 V0 & GWT 750 NF13	NATURAL	C
2322917-2	2			10	5		NATURAL	C
2315717-1	2			10	5		NATURAL	C
2315717-2	2			10	5		NATURAL	C
2315717-3	2			10	5		NATURAL	C
1-2315717-2	2			10	5		NATURAL	E
2-2315717-2	2	4	0.5	10	5		NATURAL	E
2315717-4	4			20	15		NATURAL	C
2315717-5	4			20	15		NATURAL	C
2315717-6	3			15	10		NATURAL	C
2315717-7	3			15	10		NATURAL	C
1-2315717-3	3			15	10		NATURAL	E
PART NO.	POS	DIM C 12	DIM D 12	DIMA 12	DIM B 12	MATERIAL	COLOUR	REV.

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

P

LYR

REVISIONS

DESCRIPTION

DATE

DWN

APVD

SEE SHEET-01

2.00

0-969484-1

2.14

1-969484-1
2315717-2

2.13

2-969484-1

2.12

3-969484-1 OBSOLETE

2.11

4-969484-1

2.10

5-969484-1 OBSOLETE

2.09

6-969484-1

2.07

7-969484-1 OBSOLETE
3-2364739-2

2.06

8-969484-1

2.04

9-969484-1 OBSOLETE

2.03

0-969484-2

2.02

1-969484-2 OBSOLETE

2.08

2-969484-2

2.21

3-969484-2

2.99

4-969484-2
2315717-1

2.20

5-969484-2
2-2364739-2

2.19

6-969484-2

2.18

7-969484-2

2.17

8-969484-2
2315717-3

2.16

9-969484-2

2.31

0-969484-3

2.15

1-969484-3 OBSOLETE

2.05

2-969484-3 OBSOLETE

2.30

3-969484-3 OBSOLETE

Ohne/None

4-969484-3

Ohne/None

5-969484-3

Ohne/None

6-969484-3

Ohne/None

7-969484-3 OBSOLETE

Ohne/None

5-1241961-2

Ohne/None

0-1241961-1

PA6

2-1241961-2

PA6

3-1241961-2

PA6

6-1241961-2
2364739-2

PA6

7-1241961-2
2-2315717-2

PA6

8-1241961-2
8-2178412-2

PA6

9-1241961-2

PA6

0-1241961-3
1-2315717-2

PA6

3-1241961-3 OBSOLETE

PA6

4-1241961-3

PA6

5-1241961-3

PA6

6-1241961-3

PA6

7-1241961-3
1-2364739-2
2178571-2

PA6

6-1241983-2

PA6

8-1241983-2

PA6

5-1241983-3

0-1241983-2

1-1241983-2

2-1241983-2

3-1241961-1

8-1241961-3
2322917-2

4-1955422-3

9-1955506-2

0-1955422-1

PRELIMINARY

3.00

0-969484-6 OBSOLETE

3.38

1-969484-6 OBSOLETE

3.18

2-969484-6

3.37

3-969484-6

3.35

4-969484-6 OBSOLETE

3.33

5-969484-6 OBSOLETE

3.32

6-969484-6 OBSOLETE

3.20

7-969484-6

3.10

8-969484-6

3.09

9-969484-6

3.08

0-969484-7 OBSOLETE

3.39

1-969484-7
1-1955422-7

3.31

2-969484-7 OBSOLETE

3.40

3-969484-7

3.99

4-969484-7 OBSOLETE

Ohne/NONE

5-969484-7

3.45

6-969484-7 OBSOLETE

3.47

7-969484-7 OBSOLETE

3.65

8-969484-7

3.48

9-969484-7 OBSOLETE

3.66

0-969484-8

Ohne/NONE

1-969484-8 OBSOLETE

Ohne/NONE

2-969484-8

Ohne/NONE

9-1241961-9

Ohne/NONE

3-1241961-8

Ohne/NONE

9-969484-9

Ohne/NONE

4-1241961-8

Ohne/NONE

5-1241961-8

PA6

0-1241961-6

PA6

2-1241961-7
5-1241961-7
2364739-3
2178571-1

PA6

1-1241961-8

PA6

2-1241961-8
1-2364739-3

PA6

6-1241961-8
7-1241961-7

PA6

7-1241961-8

PA6

1-1241961-7

PA6

8-1241961-8
1-2315717-3

03-K

2-1241817-3

PA6

0-1241961-8

03-F

3-1241961-7
3-2178412-7
3-2178413-7

03-I

4-1241961-7
4-2178412-7
4-2178413-7

03-G

5-1955422-7
5-1241961-7
1-1241961-9
0-1955422-6
6-2178575-7
2345753-1

Ohne/NONE

9-1241961-7

Ohne/NONE

0-2315717-6

Ohne/NONE

0-2315717-7

4 POSITION VARIANTS

4

0-1241959-4
0-1241817-4
2364739-4
2178571-3

4

2-1241959-4

4

4-1241959-4
2315717-4

PRELIMINARY

0-1955507-4

4

0-2315717-5

4

2-1241817-4

4

3-1241817-4 OBSOLETE
2322164-1
2322917-4

5

0-1241959-5
2364739-5

5

0-1241817-5

5

2-1241817-5

5

1-2178571-3
2-2178571-3

5 POSITION VARIANTS

5

0-1241959-5
2364739-5

5

0-1241817-5

5

2-1241817-5

5

1-2178571-3
2-2178571-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Kishor M 18-10-07

CHK K.Munz 18-10-07

APVD T.Klenner 18-10-07

PRODUCT SPEC 108-18049

APPLICATION SPEC

MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES FINISH ±°

WEIGHT -

Customer Drawing

NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II

SIZE A1

CAGE CODE 00779

DRAWING NO. 1241961

RESTRICTED TO -

SCALE 5:1

SHEET 4 OF 4

REV E9

4805 (3/11)