



Ti2 Series



HW (Form E)



AH (Form A)




Switching Operation

1 NC / 1 NO Contacts


Slow Action

608.8121.015
TI2-U1Z HW




Snap Action

608.8171.016
TI2-SU1Z HW




Slow Action

608.8135.021
TI2-U1Z AH




Snap Action

608.8185.022
TI2-SU1Z AH




2 NC Contacts


608.8821.017
TI2-A2Z HW




608.8871.018
TI2-SA2Z HW



608.8835.023
TI2-A2Z AH



608.8885.024
TI2-SA2Z AH



2 NO Contacts

-

608.8871.020
TI2-SE2 HW



-

-

1 NC / 1 NO Contacts Overlapping

-

-

-

-

Replacement actuator:

391.8191.547

391.8351.166

Technical Information

	Slow Action	Snap Action
Maximum Switching Voltage	240V	240V
Maximum Switching Amperage	10A	10A
B10d	6 Million	6 Million
Mechanical Service Life	3 x 10 ⁶	3 x 10 ⁶
Switching Frequency	≤ 100/min	≤ 100/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65
Utilization Category	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	240VAC	240VAC
Approvals		



Special features/variants (on request)

- Available with different actuating directions
- With steel roller
- Various roller diameters

	Slow Action	Snap Action
Maximum Switching Voltage	240V	240V
Maximum Switching Amperage	10A	10A
B10d	6 Million	6 Million
Mechanical Service Life	3 x 10 ⁶	3 x 10 ⁶
Switching Frequency	≤ 100/min	≤ 100/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65
Utilization Category	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	240VAC	240VAC



Special features/variants (on request)

- Available with different actuating directions
- With steel roller
- Various roller diameters
- Offset or straight lever
- Various lever lengths
- With roller over switch

Drawing dimensions in mm