



CII

TE Internal #: 1617127-8

TO-5/.100 Grid Relays, Contact Arrangement 2 Form C, DPDT, 2 C /O, 14VDC Input Voltage, Without MOSFET Driver, Without Transistor Driver

View on TE.com >

Relays, Contactors & Switches > Relays > Mil-Aero Relays > TO-5/.100 Grid Relays



Contact Arrangement: 2 Form C, DPDT, 2 C/O

Input Voltage: 14 VDC

Coil Suppression Diode: Without

MOSFET Driver: Without

Transistor Driver: Without

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

Configuration Features

Transistor Driver	Without
-------------------	---------

Electrical Characteristics

Coil Magnetic System	Non-Polarized, Monostable
Vibration	30G's, 10 – 3000Hz
Actuating System	DC
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
Input Voltage	14 VDC
Coil Suppression Diode	Without
Coil Voltage	26.5 VDC
Coil Resistance	3300 Ω



Coil Power Rating (DC)	213 mW
Coil Polarity Protection Diode	Without
Contact Switching Voltage (Max)	28

Contact Features

Contact Current Class	Low Level – 1 A
Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Current Rating	1 A

Termination Features

Termination Type	PC Pins
------------------	---------

Mechanical Attachment

Mounting Type	Printed Circuit Board
---------------	-----------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Model / Part # 2-1617030-7
HFW1201G01M = M39016/6-116M

Customers Also Bought

TE Model / Part #4-2176392-5
RQ 1206 383K 0.1% 10PPM 5K RL

TE Model / Part #1-1617119-9
J1MAWD-5XM = M39016/23-013M

TE Model / Part #5-103165-8
24 MODII HDR DRRRA 3/4SHRD LF

TE Model / Part #CM0967-000
D-150-0348

TE Model / Part #CR9761-000
D-200-0231-SF-C

TE Model / Part #F87083-000
DK-621-L934-1S

TE Model / Part #YDTS24F17-26BNV001
RECP ASSY

TE Model / Part #YDTS26F25-37BBV001
PLUG ASSY

TE Model / Part #YDTS26F25-37BNV001
PLUG ASSY

TE Model / Part #4-1617033-1
HFW1231K05M = M39016/6-125M

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model



[ENG_CVM_CVM_1617127-8_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617127-8_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617127-8_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MS](#)

English