








PRODUCT NUMBER
10132169-B00XLf





VIEW WITHOUT MYLAR

RECOMMENDED PLUG
ø3.5 4-POLE STANDARD PLUG

PCB HOLES (BOTTOM VIEW) t=1.2mm
NOTE: GENERAL TOLERANCE: ±0.05mm

SCHEMATIC
(CODE: B)

PLUG inserted



NOTES:



1. MATERIAL: SEE MATERIAL TABLE.
2. PRODUCT SPECIFICATION: GS-12-1160.
3. PACKAGE SPECIFICATION: GS-14-2338.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004.
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE 5 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
6. PART NUMBER DEFINITION:
10132169-X X X X Lf

LEAD FREE
MYLAR - BLANK; WITH MYLAR; N: NO MYLAR
PLATING - 0: Ag
HSG COLOR - 0: BLACK
CIRCUIT SCHEMATIC CODE


NO.	PART NAME	TER'NO.	QTY.	MATERIAL	REMARK
⑦	MYLAR	1	1	MYLAR t=0.11	
⑥	SHUNT TERMINAL	6,7	2	BRASS t=0.20	Ag-PLATED
⑤	SHUNT TERMINAL	5	1	BRASS t=0.20	Ag-PLATED
④	RING TERMINAL	3,4	2	STAINLESS STEEL t=0.20	Ag-PLATED
③	TIP TERMINAL	2	1	STAINLESS STEEL t=0.20	Ag-PLATED
②	EARTH TERMINAL	1	1	STAINLESS STEEL t=0.20	Ag-PLATED
①	HOUSING		1	PA9T 94V-0	BLACK

mat'l. code	surface	tolerance	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified
A	TAI	2014-10-31	16<L≤63 ±0.4	angles
B	ELX-T-20758	TAI	2015-06-08	4<L≤16 ±0.3
			X°±5°	L≤4 ±0.2
			dr	KENNY TAI 2014-10-31
			enr	KENNY TAI 2014-10-31
			chr	KENNY TAI 2014-10-31
			appd	PM ZHENG 2014-10-31
sheet index	revision sheet	B 1	B 2	

title	dwg no	sheet 1 of 2	size
3.5mm PHONE JACK	10132169		A4
type	CUSTOMER Drawing		




1 Carton
= 6 Reel/ Carton
= 500 pcs / reel
= 3000 pcs/Carton



NOTE:

1.CARRIER TAPE PACKING LENGTH
TRAILER CONNECTORS LEADER(START)



2.FEELING FORCE: 0.1N-1.3N (10g-132g)

NOTE:

- 1.Reel (330X28.4mm)
- 2.Carton (360X360X220mm)
- 3.Carton thickness = 6.0mm
- 4.Unit:mm
- 5.N.W=1.44Kg; G.W=3.7Kg

mat'l. code				surface	tolerance	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
					angles	16<L≤63 ±0.4	3.5mm PHONE JACK			
					4<L≤16 ±0.3	MM				
					X°±5°	L≤4 ±0.2	scale			
					dr	KENNY TAI	2014-10-31	dwg no		sheet 2 of 2
					enr	KENNY TAI	2014-10-31	10132169		size
					chr	KENNY TAI	2014-10-31			A4
					appd	PM ZHENG	2014-10-31	type		CUSTOMER Drawing
sheet index	revision sheet	B	B	1	2					