

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D5	REVISED PER ECR-18-001421	30JAN2018	JH	PKS

- 1
- SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG,
0.16MM(.006")-1.02MM(.040") DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
MALE BLADE 0.5MM(.020") THICK BRASS




- 2
- POCKET RECOMMENDATION: #1601425

- 3
- TERMINALS TO BE APPLIED PER TYCO ELECTRONICS
SPECIFICATION 114-13166 FIGURE 11.

- 4
- PRODUCT SPECIFICATION: STANDARD SIAMEZE 108-2085

- 5
- PRODUCT SPECIFICATION: HIGH TEMPERATURE 108-2293

- 6
- PRELIMINARY-FOR QUOTATION



5	EXTRA HARD CU ALLOY	UNPLATED	-	6	4-1601075-4
5	EXTRA HARD CU ALLOY	UNPLATED	-	6	2-1601075-4
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	031-145-014		4-1601075-2
4	BRASS, SPRING HARD	UNPLATED	031-145-014		4-1601075-1
4	BRASS, SPRING HARD	POST TIN PLATE OVER NICKEL UNDERPLATE	-		2-1601075-3
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-146-014		2-1601075-2
4	BRASS, SPRING HARD	UNPLATED	131-146-000		2-1601075-1
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-145-014		1601075-2
4	BRASS, SPRING HARD	UNPLATED	131-145-000		1601075-1
MATERIAL		FINISH	REFERENCE PART NUMBER	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002	TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		CHK M.FEHER 11JAN2002			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.RANDOLPH 11JAN2002			
0 PLC ± - 1 PLC ± 0.25 [.010] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC APPLICATION SPEC			
MATERIAL SEE TABLE		FINISH SEE TABLE	NAME STANDARD RANGE WIRE TO BLADE, SIAMEZE TERMINAL		
		WEIGHT 0.000000	SIZE A2	CAGE CODE 00779	DRAWING NO C=1601075
		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 1	REV D5