





FIXING PLATE

164A19579X
CONEC ABC

see note 8


NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- PLASTIC BRACKETS: PBT GF UL 94 V-0; BLACK
- THREADED LOCKS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- FIXING-PLATE: PBT GF UL 94 V-0; BLACK
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: **164A19579X CONEC ABC**



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale:		2:1 (5:1)		
								material:		see notes		
						date	name		title: D-SUB FEMALE 90° 25pos. SOLDER PIN ANGLED 0.590inch threaded lock, plastic bracket, fixing plate			
					drawn	01.12.10	Schmidt					
					appd.	01.12.10	Fischer					
					norm							
					d-old			dwg no:		DIN-A3 sh: 1		
									16K1A2729			
	a	Origin							part no:		164A19579X	
	rev.	description	date	name								



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale:	3:1
							material:	see sheet 1
							title: P.C.B. HOLE DRILLINGS 25pos. SOLDER PIN ANGLED 0.590inch threaded lock, plastic bracket, fixing plate	
							dwg no:	DIN-A3
							sh: 2	
DO NOT ALTER CAD DRAWING BY HAND						part no: see sheet 1		
rev.	a	Origin		date	01.12.10	name	Schmidt	
description				date	01.12.10	name	Fischer	
				norm				
				d-old				