










PM Series

Standard Size Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
Contact rating: 6 Amps at 125 VAC, 3 Amps at 250 VAC Initial contact resistance: 30 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 1000 VAC for 1 minute (min.) Electrical life: 10,000 cycles min. Operating temperature range: -20°C to +60°C Actuation force: 500g ± 200g Solder heat resistance: 260°C max. for 3 seconds Solvent washing permissible	- Wash-through open frame construction. - UL & CSA recognized. - Threaded mounting holes standard - M3X0.5. - Panel mounting.
MATERIALS	
Contacts: Silver plated phosphor bronze Terminals: Tin plated brass Base: Phenolic laminated sheet	Actuator: Nylon, type 6/6 Frame: Zinc plated steel

MODEL NO. PM13B012		1P2T	 ● = COMMON	 MECHANICAL OUTLINE	 PANEL CUTOUT
MODEL NO. PM13B022		2P2T	 ● = COMMON	 MECHANICAL OUTLINE	 P. C. BOARD LAYOUT
MODEL NO. PM13B022P		2P2T	 ● = COMMON	 MECHANICAL OUTLINE	 PANEL CUTOUT