




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

1

MATERIAL HOUSING : GREY GLASSFILLED POLYESTER.
MATERIAL CONTACTS: PHOSPHORBRONZE.

2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION
PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3

CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.

4

CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.

5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III,
CENTRAL OFFICE APPLICATIONS.

6

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III,
UNCONTROLLED ENVIRONMENT APPLICATIONS.

7

CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.

8

CONTACT CAVITIES (3x) SUITABLE FOR 4,8 DIA. HIGH CURRENT,
HIGH FREQUENCY OR FIBRE OPTIC CONTACTS AS PER DIN 41626
(SEE ALSO NOTE 12).

9

CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
THE MARKING CAN APPEAR ON THE FRONT SIDE OR ON THE BACK SIDE.

10

AREA RESERVED FOR KEYING PART, BASIC P/N 100526.

11

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (55 HOLES).

12

1,3 DIA. PLATED-THROUGH HOLES (15x) CAN BE OMITTED
IF SPECIAL CONTACTS WITH CABLE CONNECTION OR FIBRE
OPTIC CONTACTS ARE USED.

13

THIS ROW OF 11 CAVITIES (B1 TO B11) FOR
CONNECTOR ASSEMBLY PURPOSE ONLY.

14

NOT PLATED-THROUGH HOLES (3x).

15

FITS WITH INTEGRATED GROUND RETURN UPPERSHIELD,
BASIC P.N. 5352111 AND INTEGRATED GROUND
RETURN LOWERSHIELD, BASIC P.N. 5352112

16

CONNECTOR ASSEMBLED WITH REDESIGNED CONTACTS.
CONTACTS HAVE A CORING-OUT IN THE PLASTIC.

17

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5100750

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

K.N.KIRAN

10AUG2004

CHK

B. MOOIJ

23SEP2004

APVD

B. MOOIJ

23SEP2004

PRODUCT SPEC

108-19082

APPLICATION SPEC

114-19029


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2

FINISH

-



TE Connectivity

NAME

Z-PACK 2mm HM
TYPE M FEMALE CONNECTOR
-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=5100750

RESTRICTED TO

-

SCALE

5:1

SHEET

2 of 2

REV

D

1471-9 (1/15)