


SCHOTTKY BARRIER DIODE
FEATURES

- Small Surface Mount device
- Low forward voltage drop
- High surge current capability
- Epitaxial construction


SMB

MECHANICAL DATA

- Case: SMB(DO-214AA)
- Case Material: Molded Plastic. UL flammability
- Classification Rating: 94V-0
- Weight: 0.088 grams (approximate)

MAXIMUM RATINGS AND CHARACTERISTICS($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	SK52	SK53	SK54	SK55	SK56	SK59	SK510	SK515	SK520	Unit
Marking		SK52	SK53	SK54	SK55	SK56	SK59	SK510	SK515	SK520	
Repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	200	V
RMS Reverse Voltage	V _{RMS}	14	21	28	35	42	56	70	105	140	V
DC Reverse Voltage	V _R	20	30	40	50	60	90	100	150	200	V
Non-Repetitive Peak Forward Surge Current @ t = 8.3 ms	I _{FSM}	150									A
Maximum Average Forward Rectified Current	I _F	5.0									A
Typical thermal resistance (NOTE 1)	R _{θJA}	55.0									°C/W
	R _{θJL}	17									°C/W
Junction Temperature	T _J	-50 ~+125					-50 ~+150				°C
Storage Temperature	T _{STG}	-50 ~+150									°C

Note: 1. P.C.B. mounted with 0.2x0.2" (5.0x5.0mm) copper pad areas

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise specified)


Parameter	Symbol	SK52	SK53	SK54	SK55	SK56	SK59	SK510	SK515	SK520	Unit	Conditions
Forward voltage	V _F	0.55			0.70		0.85		0.90	0.95	V	I _F =5A
Reverse current T _A =25°C	I _R	0.5									mA	V=V _R
Reverse current T _A =100°C	I _R	20			10					mA		
Junction capacitance	C _J	200			300					pF	V _R =4V,f=1MHZ	

SCHOTTKY BARRIER DIODE

Typical Characteristics


AVERAGE FORWARD RECTIFIED CURRENT,
AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE




PEAK FORWARD SURGE CURRENT,
AMPERES

FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




INSTANTANEOUS FORWARD
CURRENT,AMPERES

FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




INSTANTANEOUS REVERSE CURRENT,
MILLIAMPERES

FIG. 4-TYPICAL REVERSE CHARACTERISTICS




JUNCTION CAPACITANCE, pF


FIG. 5-TYPICAL JUNCTION CAPACITANCE




TRANSIENT THERMAL IMPEDANCE,
°C/W

FIG. 6-TYPICAL TRANSIENT THERMAL IMPEDANCE



SCHOTTKY BARRIER DIODE
SMB Package Outline Dimensions


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	5.00	5.45	0.197	0.215
B	3.20	4.00	0.126	0.157
C	4.30	4.70	0.169	0.185
D	1.80	2.20	0.071	0.087
E	2.20	2.50	0.087	0.098
G	1.90	2.30	0.075	0.090
H	0.95	1.25	0.037	0.049
I	0.05	0.15	0.002	0.006
K	1.70	2.10	0.067	0.083
L	0.90	1.60	0.035	0.063
N	0.10	0.30	0.004	0.012


SMB Suggested Pad Layout

Note:

1. Controlling dimension: in millimeters
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purposes only

SCHOTTKY BARRIER DIODE


SMB Tape and Reel

SMB Embossed Carrier Tape




DIMENSIONS ARE IN MILLIMETER										
TYPE	A	B	C	d	E	F	P0	P	P1	W
SMB	4.10	5.50	2.58	Ø1.50	1.75	5.50	4.00	8.00	2.00	12.00
TOLERANCE	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1

SMB Tape Leader and Trailer



SMB Reel



DIMENSIONS ARE IN MILLIMETER								
REEL OPTION	D	D1	D2	G	H	I	W1	W2
13" DIA	Ø330	75.0	13.00	R165	R37.50	R6.50	12.40	17.60
TOLERANCE	±2	±1	±1	±1	±1	±1	±1	±1