




CUSTOMER DRAWING

REVISIONS			
ZONE	REV.	DESCRIPTION	DATE
	PA1	INITIAL RELEASE	2021/3/25



INNER CONTACT
QTY: 4
GOLD PLATED
SCALE 6.000




4. THE RATED VOLTAGE: 50V
THE RATED CURRENT: 5A
3. THE RECOMMEND WIRE SIZE : AWG 18~20.
2. THE CONTACT IMPEDANCE RESISTANCE 120OHM.
1. THE REFERENCED PRODUCT SHALL BE COMPLIANT TO RoHS
DIRECTIVE.

NOTES

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

Next Assembly

UNLESS OTHERWISE SPECIFIED		APPROVALS		DATE	<div>AMPHENOL CORPORATION</div> <div>Amphenol Technology (Zhuhai) Co. Ltd.</div> <div>No. 63 Xingnan Road, Sanzao Town, Jinwan, Zhuhai, PRC</div> <div>CONTACT SOCKET, QUADRAX</div> <div>QX4-20-S-120</div> <div>GOLD PLATED</div>						
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ± .0005 .XXX = ± .010 .XX = ± .03 .X = ± .1 ANGLES = ± 2° Amphenol STANDARDS PER 9-3800		PREPARED BY:	Bruce Lee	2021/3/25							
		LEAD/PRODUCT ENGINEER:	Bruce Lee								
		ENGINEERING MANAGER:	Ran Xiao								
		PRODUCT GROUP:	C&I								
		AIPG DIVISION:	AIO								
		MATERIAL SPEC		PROCESS SPEC		SIZE	CAGE CODE	DOCUMENT NUMBER		REV	
THIRD ANGLE PROJECTION		N/A		N/A		C	77820	10-765917-12S		PA1	
						SCALE: 6:1		REF:		SHEET 1 OF 1	