

Coaxial PCB Connector 85_SMC-50-0-1/111_N

Description

Right angle PCB jack

Interface Standards

IEC 60169-9_MIL-STD-348A/312_CECC 22140



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	10 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0029 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013115
Catalogue drawing	DCA-00013117

Ordering Information

Single package	85_SMC-50-0-1/111_NE
Bulk 100 pcs package	85_SMC-50-0-1/111_NH

Remarks

PCB connector with stand-offs