



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-	-	SEE SHEET 1	-	-

PCB LAYOUT
Leiterplattenanschluss






TOLERANCES UNLESS OTHERWISE SPEC. ±0.1 mm
Freimasstoleranz ±0.1 mm

SPECIAL VERSION 2 POSN.
Sondervariante 2 pol.



3-1355181-2 , 2311512-2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Weber	16MRZ99	TE Connectivity	
		CHK Schnaubelt	06JUL99		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP DUOPLUG 2,5 WITH PCB LOCKING DEVICE DGB 11	
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±2° FINISH		PRODUCT SPEC	
				APPLICATION SPEC	
MATERIAL SEE TABLE		WEIGHT -		SIZE A100779	
		CUSTOMER DRAWING		SCALE 10:1	
				SHEET 2 OF 2	
				REV E3	