







712A



722A



732A



NOTES:

1. DIMENSIONS SHOWN FOR REFERENCE ONLY.
2. HEX NUT AND FLAT WASHER SUPPLIED UNASSEMBLED.
3. MATERIAL:

HOUSING, HEX NUT - COPPER ALLOY, NICKEL PLATED
 INSULATOR HOUSING - THERMOPLASTIC, BLACK
 TERMINAL INSULATORS - PHENOLIC
 FLAT WASHER - STEEL, NICKEL PLATED
 PIN, SPRING, TERMINALS - COPPER ALLOY, SILVER PLATED
4. IT IS RECOMMENDED THAT THE JACK MOUNTING NUT BE TIGHTENED SNUG BY HAND BEFORE APPLYING A FINAL TIGHTENING TORQUE OF 8-10 LB-IN USING HAND TOOLS ONLY. POWER DRIVER OR IMPACT DRIVERS ARE NOT RECOMMENDED.
5. THESE PRODUCTS ARE RoHS COMPLIANT

SCHEMATIC

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M	TEMPER
					1. ALL DIMENSIONS IN INCHES [mm]					
					- TWO PLACE DECIMALS ± 0.02 [0.5]					
					- THREE PLACE DECIMALS ± 0.005 [0.13]					
J	28397	06-11-21	PC	TJK						FIRST USED ON
H	27884	05-04-17	PC	TJK						SCALE 3:1
REV	ECO NUMBER	DATE	BY	APVD	DATE DRAWN	BY	CHKD	APVD		Switchcraft®
					09-27-17	PC	PC	09-27-17	09-27-17	SHEET 1 OF 1
					NAME	POWER JACKS 7_2A SERIES, RoHS				
					PART No.	712A 722A 732A				
					REV	J				
					DO NOT SCALE DRAWING					
					REVISIONS					