

4 3 2 1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECR-07-006768	05APR07	HMR	GJ

- DIMENSIONS SPECIFIED MAY VARY PER CUSTOMER APPLICATION, DO NOT TOOL WITHOUT TYCO ELECTRONICS REVIEW AND APPROVAL.
- TYCO ELECTRONICS REQUIRES THE FOLLOWING INFORMATION IN ORDER TO APPROVE THE CUSTOMERS APPLICATION DRAWING MAGNET WIRE RANGE, LEAD WIRE RANGE AND INSULATION THICKNESS.
- MAGNET WIRE COIL MUST NOT EXCEED HEIGHT OF MAGNET WIRE SLOT AS SHOWN UNLESS PROVISIONS ARE MADE TO KEEP "FINISH" WIRE FLAT AGAINST BASE OF WIRE SLOT.
- MATERIAL RECOMMENDED: NYLON 6/6 AND NYLON 6/6 30% GLASS FILLED. OTHER MATERIALS ARE ACCEPTABLE HOWEVER, CONSULT TYCO ELECTRONICS FOR SPECIFICATIONS.
- 30 AWG. (ϕ .01 [0.26]) WIRE AND FINER REQUIRES WIRE WRAP POST INSTEAD OF TRIM POST. SEE SPEC. DRW. #1601447.
- MUST MAINTAIN SLOT THICKNESS (.0235) [0.60] INCLUDING DRAFT ANGLE FROM BOTTOM OF POCKET TO .015[0.38] MINIMUM ABOVE BASE OF WIRE SLOT. (.029[0.74] MAX.THICKNESS AT TOP).
- WHENEVER POSSIBLE, POCKET PITCH TO MATCH TERMINAL PITCH. MINIMUM PITCH TO BE .197 [5.00].
- .060 [1.52] MIN. WALL THICKNESS RECOMMENDED ON TRIM POST SIDE WHEN WIRE TRIMMING IS REQUIRED.
- SIZE THIS SLOT FOR LARGEST WIRE DIA. CONSULT MOLD VENDOR IF SMALLER THAN .020 [0.51] IS TO BE SPECIFIED.
- REFER TO TABLE. CONSULT TYCO ELECTRONICS IF WIRE SIZE TO BE USED, OVERLAP THE RANGES SHOWN.
- SLOT DEPTH DIMENSIONS ARE FOR CONNECTING ONE MAGNET WIRE WITH A MOVING BEAM SIAMEZE CONTACT. CONSULT TYCO ELECTRONICS FOR BIFILAR (2 WIRE) CONNECTIONS.

.060 [1.52] MIN. OUTER SIDE WALLS

WRAP POST 5

TRIM POST 5

.030 [0.76]

.220 ±.003 [5.59±0.08] PITCH RECOMMENDED 7

.156 ±.003 [3.96±0.08] -A- MAGNET WIRE SLOT 9

.025 [0.63] SLOT DEPTH "X" 3 10

.230 [5.84]

R.015 [.38] TYP

.040 [1.02] MIN.

.070 [1.78] FULL RADIUS (BASE OF WIRE SLOT)

.050 [1.27]

15° TYP.

SECTION A-A

.040 [1.02] MIN. TYP 8

.0235 ±.0015 [0.60±0.04] 6

15°

.003 [0.08] R. MAX

WIND HEIGHT 3

SECTION B-B

MAGNET WIRE SIZE AWG [mm DIA]	SLOT DEPTH "X" ±.003 [±0.08] 11
#18-#21.5 [1.02-0.69]	.135 [3.43]
#22-#25.5 [0.65-0.43]	.123 [3.12]
#26-#29.5 [0.41-0.27]	.115 [2.92]
#30-#33.5 [0.25-0.17]	.110 [2.79]
#34-#36 [0.16-0.13]	.107 [2.72]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05APR2002 MICHAEL S. FEHER	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK 05APR2002 GENE JACONO	NAME KURT A. RANDOLPH	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 05APR2002 KURT A. RANDOLPH	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		114-13166		
2 PLC ± .01 [0.25]		WEIGHT -		
3 PLC ± .005 [0.13]		SIZE A2 CAGE CODE 00779 C=1601424		
4 PLC ± .0010 [0.026]		DRAWING NO 1601424		
ANGLES ± 2°		RESTRICTED TO -		
MATERIAL 4		SCALE 4:1 SHEET 1 OF 1 REV B		
FINISH -		CUSTOMER DRAWING		

AMP 1471-9 REV 31MAR2000