






- ① MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- ② FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- ③ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- ⑤ FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



LEFT GUDIED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN	K_SHOBER	ZZDEC1T			TE Connectivity
						CNR	EABY	ZZDEC1T			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APRD	EABY	ZZDEC1T	NAM	IMPACT, 3 PAIR, 10 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
		0 PLC ±0.25				PRODUCT SPEC -					
		2 PLC ±0.13				APPLICATION SPEC					
		3 PLC ±0.13						SZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	4 PLC ±0.13				WEIGHT -		A1	00779C-2007777	-	
	SEE TABLE	5 PLC ±0.13				CUSTOMER DRAWING		SCALE	6:1	SHEET	1 OF 2 REV C

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-

	H	5.5	8-2007777-6
	H	4.9	8-2007777-5
	H	4.5	8-2007777-4
	H	5.5	8-2007777-3
	H	4.9	8-2007777-2
	H	4.5	8-2007777-1
	G	5.5	7-2007777-6
	G	4.9	7-2007777-5
	G	4.5	7-2007777-4
	G	5.5	7-2007777-3
	G	4.9	7-2007777-2
	G	4.5	7-2007777-1
	F	5.5	6-2007777-6
	F	4.9	6-2007777-5
	F	4.5	6-2007777-4
	F	5.5	6-2007777-3
	F	4.9	6-2007777-2
	F	4.5	6-2007777-1
	E	5.5	5-2007777-6
	E	4.9	5-2007777-5
	E	4.5	5-2007777-4
	E	5.5	5-2007777-3
	E	4.9	5-2007777-2
	E	4.5	5-2007777-1
	D	5.5	4-2007777-6
	D	4.9	4-2007777-5
	D	4.5	4-2007777-4
	D	5.5	4-2007777-3
	D	4.9	4-2007777-2
	D	4.5	4-2007777-1
	C	5.5	3-2007777-6
	C	4.9	3-2007777-5
	C	4.5	3-2007777-4
	C	5.5	3-2007777-3
	C	4.9	3-2007777-2
	C	4.5	3-2007777-1
	B	5.5	2-2007777-6
	B	4.9	2-2007777-5
	B	4.5	2-2007777-4
	B	5.5	2-2007777-3
	B	4.9	2-2007777-2
	B	4.5	2-2007777-1
	A	5.5	1-2007777-6
	A	4.9	1-2007777-5
	A	4.5	1-2007777-4
	A	5.5	1-2007777-3
	A	4.9	1-2007777-2
	A	4.5	1-2007777-1
	-	5.5	2007777-6
	-	4.9	2007777-5
	-	4.5	2007777-4
	-	5.5	2007777-3
	-	4.9	2007777-2
	-	4.5	2007777-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. K. SHOBER	22DEC11	TE Connectivity		
			CHK	J. EABY	22DEC11	NAME IMPACT, 3 PAIR, 10 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH		
			APVD	J. EABY	22DEC11			
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC		
mm			9 PLC			±.025		
			3 PLC			±0.13		
			5 PLC			±		
			4 PLC			±		
			ANGLES			±		
			FINISH			±		
MATERIAL			SEE TABLE			WEIGHT		
-			-			-		
			CUSTOMER DRAWING			SIZE		
						A100779C=200777		
						RESTRICTED TO		
						-		
						SCALE		
						5:1		
						SHEET		
						2		
						OF		
						2		
						REV		
						C		