

BG GHDE LED TL M4 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Energy-efficient basic lighting with a long service life

- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	1390870000
Type	BG GHDE LED TL M4 PT6
GTIN (EAN)	4050118191059

BG GHDE LED TL M4 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	46 mm	Height (inches)	1.811 inch
Width	104 mm	Width (inches)	4.094 inch
Length	181 mm	Length (inches)	7.126 inch
Net weight	566 g		

Temperatures

Operating temperature	-40 °C...60 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3	SCIP	730dada5-5c8b-4737-8e0b-847db05
------------	--	------	---------------------------------

General data

Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Circuit breaker	< 10 A	Halogen	yes (PVC cable)
Height	≤ 3000 m	Insulation voltage	< 500 V (housing/PE)
LED operating life	> 50.000 h	Line type	Heluwind WK 103w-T 3G1,5 (AD 8 mm)
Mounting position, installation notice	Arbitrary	Peak acceleration, type L	70 m/s ²
Pollution severity	2	Protection class	II
Protection degree	IP65	Shape of the LED module	Other
Shock resistance EN 60721-3-3	Class 3M3	Short-circuit protection	internal
Silicone	No	Surge voltage category	II
Type of connection	Open cable end/length 2 m	UL 94 flammability rating	V-0
Vibration resistance EN 60721-3-3	Class 3M3, EN 60721-3-3		

Rated data acc. to IEC 60598-1

Input voltage	100...265 V DC (45...65 Hz)	Inrush current	0.5 A @ 0.1 ms
Power loss	< 2 W	Power rating	7 W
Rated voltage	265		

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ECLASS 9.1	27-11-06-35
ECLASS 10.0	27-11-06-35	ECLASS 11.0	27-11-06-35
ECLASS 12.0	27-11-06-35		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E345151

Creation date September 16, 2022 4:27:05 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

BG GHDE LED TL M4 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[FieldPower LED](#)

Catalogues

[Catalogues in PDF-format](#)

BG GHDE LED TL M4 PT6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

