




NOTES:

- METALSHELLS: STEEL; min. $315\mu\text{in}$ TIN over $40\text{--}80\mu\text{in}$ NICKEL
- INSULATOR: PBT GF UL 94 V-0; GREEN
- HIGH POWER CONTACTS 20A COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
PLATING TERMINATION SIDE: $160\text{--}240\mu\text{in}$ TIN over $80\mu\text{in}$ NICKEL
- THREADED SPACER CLIPS: COPPER ALLOY; min. $200\mu\text{in}$ TIN over $80\mu\text{in}$ NICKEL
PCB-HOLE: $\varnothing 3,1 \pm 0,1$; PCB THICKNESS 2,3mm
- COLLARS: COPPER ALLOY; min. $200\mu\text{in}$ TIN over $80\mu\text{in}$ NICKEL
- P.C.B. HOLE DRILLINGS SEE SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3008W8PXX69E40X CONEC ABC

Directive 2002/95/EC RoHS compliant


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance			dim. in mm
rev.	description	date	name	date	name		
a	Original			drawn	23.02.12	Lehmenkühler	
				appd.	23.02.12	Koch	
				norm			
				d-old			

CONEC

scale:		2:1 (5:1)	
material:		SEE NOTES	
title:			
D-SUB COMBINATION MALE			
8W8P			
with threaded spacer clip			
dwg no:		DIN-A3	
13K1A3910		sh: 1	
part no:		3008W8PXX69E40X	



P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 3:1					
							material: SEE SHEET 1					
								date	name	title: P.C.B. HOLE DRILLINGS D-SUB COMBINATION MALE 8W8P with threaded spacer clip		
								drawn	23.02.12			Lehmenkühler
								appd.	23.02.12			Koch
								norm				
				d-old			dwg no: 13K1A3910					
a	Original								DIN-A3			
rev.	description	date	name				part no: SEE SHEET 1		sh: 2			