

2450 MHz Ceramic Chip Antenna Evaluation Board




ACAG0801-2450-EVB

90.0 x 50.0 mm


Description

ACAG0801-2450-EVB Evaluation boards are designed to provide a means to facilitate engineering evaluation of the chip antenna : ACAG0801-2450-T working at 2450 MHz. With a typical bandwidth of 180 MHz, the chip can be used for applications including but not limited to Wi-Fi, Bluetooth, BLE and ISM.

To evaluate the performance of antenna, calibrate the Vector Network analyzer (VNA) for the testing frequency band and connect the evaluation board to the calibrated port using the given SMA connector on the board.




2450 MHz Ceramic Chip Antenna Evaluation Board




ACAG0801-2450-EVB

90.0 x 50.0 mm

Evaluation Board with Chip Antenna Layout



Evaluation Board:



Evaluation Board dimension : 90 x 50 mm

Unit: mm


2450 MHz Ceramic Chip Antenna Evaluation Board



ACAG0801-2450-EVB

90.0 x 50.0 mm


Chip Antenna Layout



Unit: mm

Matching Network on EVB:

Antenna matching network is designed using a combination of capacitor (1.5 pF) and inductor (4.3 nH) near the input terminal as shown in the above figure.



Note :

1. Yellow highlighted space represents the ground clearance area around the chip antenna.
2. Desired clearance area : 10.0 x 7.0 mm
3. Width of the 50 Ω line is designed in accordance with the PCB thickness and material considered.
4. Matching network (Pi - network) provided is in accordance with the EVB layout and matching will differ in the actual customer PCB depending on the layout.


2450 MHz Ceramic Chip Antenna Evaluation Board



ACAG0801-2450-EVB

90.0 x 50.0 mm

Chip Antenna Dimension



Unit: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-19

ABRACON IS
ISO9001-2015
CERTIFIED