

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HB

DIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	03-Dec-15	YS.H	HL.C
	E1	ADD NEW PN ECO-18-008228	25-May-18	WQ.Y	K.T

PART A

PART B

TE

OJE-SH-112LMH



8A 250V ~

OEG C

SEE NOTE 5

LOT NO.

MADE IN CHINA

18.2±0.5




10.2±0.5

7.6±0.2

12.7±0.2

1.71

2.54±0.2



CONNECTION FIGURE





FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- 0 PLC ± -
- 1 PLC ± -
- 2 PLC ± -
- 3 PLC ± -
- 4 PLC ± -
- ANGLES ± -

FINISH

DWN H.SASAKI

CHK Y.OIKAWA

APVD S.NAGAI

PRODUCT SPEC

SEE PRODUCT SPEC

APPLICATION SPEC

—

WEIGHT —

CUSTOMER DRAWING



TE Connectivity

NAME

OJE-SH-LMH CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

1461403

SCALE 5:1

SHEET 1 of 2

REV E1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HB	—						
			—	SEE SHEET 1	—	—	—

E1

E1

E1

C	B	1461403-7	OJE-SH-124LMH	107-84031	24V	OJE-SH-124LMH	g
D	A	1461403-5	OJE-SH-124LMH	107-79010	24V	OJE-SH-124LMH	f
		1461403-4	OJE-SH-112LMH	107-79010	12V	OJE-SH-112LMH	e
		1461403-2	OJE-SH-109LMH	107-79010	9V	OJE-SH-109LMH	d
		1461403-1	OJE-SH-106LMH	107-79010	6V	OJE-SH-106LMH	c
		1461403-3	OJE-SH-105LMH	107-79010	5V	OJE-SH-105LMH	b
		1461403-6	OJE-SH-103LMH	107-79010	3V	OJE-SH-103LMH	a
FIG		TE PART NO	TE TYPE NAME	PACKAGE SPEC	PART B	PART A	TYPE

REFLAY TYPE

- NOTES:
- 1.ALL LOGO TO BE SCALE DOWNED
 - 2.FONT IS AIARL NARROW.
 - 3.PRODUCT SPECIFICATION AS SHOWN AT TABLE
 - 4.USE LASER MACHINE TO PRINT.

FIG A 5.LOT NO. SYSTEM AS FOLLOWING:






FIG B 5. LOT NO.SYSTEM AS FOLLOWING:



		UV RESIN	SEEL (VENT HOLE)	16
		EPOXY RESIN	SEEL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
FIG C	94V-0	LCP	CARD	9
FIG D	94V-0	P.P.S	CARD	
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

DWN
H.SASAKI

CHK
Y.OIKAWA

APVD
S.NAGAI

PRODUCT SPEC
SEE PRODUCT SPEC

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
OJE-SH-LMH CUSTOMER DRAWING

SIZE
A3

CAGE CODE
000779

DRAWING NO
C- 1461403

RESTRICTED TO
—

SCALE
5:1

SHEET
2 of 2

REV
E1

1470-19 (3/11)