


FLEX STACK

SMT MICRO BOARD HEADER

(1.00 mm) .0394" PITCH • MW SERIES



MW

Mates:
CLM, MLE




SPECIFICATIONS

Insulator Material:
Top: Black LCP
Bottom: Natural LCP
Terminal Material:
Phosphor Bronze
Plating:
Au over 50 μ " (1.27 μ m) Ni
Operating Temp Range:
-55 °C to +125 °C

PROCESSING



Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max (02-30)
(0.15 mm) .006" max (31-50)*
*(.004" stencil solution
may be available; contact
ipg@samtec.com)

MW	NO. PINS PER ROW	03	PLATING OPTION	D	STACKER HEIGHT	POST HEIGHT	OPTION
	02 thru 50		-G = 10 μ " (0.25 μ m) Gold		- "XXX" = Stacker Height (in inches) (2.41 mm) .095" to (6.22 mm) .245" Example: -245 = (6.22 mm) .245"	- "XXX" = Post Height (in inches) (1.65 mm) .065" minimum Example: -065 = (1.65 mm) .065"	-A = Alignment Pin (5 positions minimum) Metal or plastic at Samtec's discretion -P = Pick & Place Pad (7 positions minimum) -TR = Tape & Reel -FR = Full Reel Tape & Reel (must order maximum quantity per reel; contact Samtec for quantity breaks)



ALSO AVAILABLE MOQ Required

End shrouds
End shrouds with
guide posts



Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

APPLICATION

EXAMPLES		
LEAD STYLE		MATED HEIGHT*
MW	CLM	
-163-065	-02	(6.35 mm) .250"
-233-065		(8.13 mm) .320"

*Processing conditions will affect mated height.

