







NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. RATING: 50mA @ 12VDC
5. OPERATING FORCE: 250 ± 50 gf
6. TRAVEL: 0.25mm ± 0.2mm
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
- ▲ 8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
9. CONTACT MATERIAL: GOLD
10. ▲ DENOTES CRITICAL PARAMETER
13. OPERATING TEMP: -40°C TO 85°C



E-SWITCH®

B	24545	CHANGED OPERATING TEMPERATURE	10/19/20	JM
A	19716	RELEASE TO PRODUCTION	02/25/11	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL1105DF250R

SCALE 4:1

DATE 2/25/2011

DR BA

DWG P010030

REV B