









1:1



LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
A1	-			AENDERUNGEN BESCHREIBUNG				
PROJECT NR.: EGAUTO1349		C3	REVISED PER ECO-11-005294			30APR11	RK	HMR



- NOTES
- 1 LEVER ASSEMBLED IN PRE-LOCKED POSITION. LEVER MUST BE LOCKED BEHIND THE DIMPLE.
 - 2 USED WITH 1420000, 1420001
 - 3 ASSIGNMENT OF CAVITIES: MAXIMUM 25% OF CONTACT CAVITIES ASSIGNED WITH CONTACTS WITH A CABLE CROSS SECTION OF 0.5mm², UNIFORMLY DISTRIBUTED OVER THE HOUSING. LARGER CABLE CROSS SECTION ARE NOT PERMISSIBLE

- Bemerkungen
- 1 Hebel in Vorraststellung montiert. Hebel muss hinter der Verriegelungsnase verrastet sein.
 - 2 Benutzt mit 1420000, 1420001
 - 3 Kammerbestückung: Maximal 25% der Kontaktkammern bestückt mit Kontakten mit Kabelquerschnitt 0.5mm², gleichmäßig verteilt über das Gehäuse ist zulässig. Grössere Kabelquerschnitte sind nicht zulässig.

1534222-2	C	964826-1	E	PBT-GF	violett/ VIOLET	4006	C,D	LEVER / Hebel, HSG., 2X16 POSN.	I	2		
		1534223-2	B	PBT-GF	blau/ BLUE	5012		COVER/ Abdeckkappe, HSG., 2X16 POSN	I	1		
1534222-1	C	964826-1	E	PBT-GF	violett/ VIOLET	4006	A,F	LEVER / Hebel, HSG., 2X16 POSN.	I	2		
		1534223-1	B	PBT-GF	gruen/ GREEN	6018		COVER/ Abdeckkappe, HSG., 2X16 POSN	I	1		
TE Connectivity ASSY-No.	REV.	TE Connectivity PART-NO.	REV.	MATERIAL	COLOUR FARBE	RAL	CODING Kodierung	DESCRIPTION Benennung	QTY.	ITEM NO.		
			DIMENSIONS: MASSEINHEITEN: mm MATERIAL - TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN 0 PLC ± ACC. TO 1 PLC ± DIN 16901-140 2 PLC ± CENTRIC TO 3 PLC ± NOMINAL DIM 4 PLC ± ANGLES/WINKEL ±° FINISH/OBERFLÄCHE/FARBE			DWN 05JUL01 G.Fischer CHK 05JUL01 B.Kirsch APVD -					NAME COVER, ASSY, MQS-HSG., 2x16 POSN. Abdeckkappe, ZSB, MQS-Geh., 2x16 pol. -	
						PRODUCT SPEC PRODUKTSPEZ 108-18924						
						APPLICATION SPEC VERARBEITUNGSSPEZ 114-18630						
						WEIGHT GEWICHT -						
						CUSTOMER DRAWING /KUNDENZEICHNUNG		SCALE MASSSTAB 2:1	SHEET BLATT	OF VON	REV C3	