


Actuator

704.115.018



<https://eao.com/p/704.115.018>

Your product:



704.115.018 Actuator

FRONT

Front bezel colour:	Nature
Front dimension:	Ø 35 mm
Front bezel material:	Aluminium

MOUNTING

Design:	flush
Mounting cut-out:	Ø 30.5 mm

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching positions:	3 positions
Mechanical lifetime:	≤50 000 cycles of operation
Switching action:	Momentary - Rest (a) - Momentary
Weight:	0.099 kg
Switching angle:	42° left / 42° right

AMBIENT CONDITION

Operating temperature: – 40 °C ... + 55 °C

IP Protection: IP65 front side

Storage temperature: – 40 °C ... + 85 °C


OTHER

Short Description: Actuator, Ø 30.5 mm, Ø 35 mm, Nature, Aluminium, Momentary - Rest (a) - Momentary

Hints: The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on


max. number of switching elements: 3

Dimension drawings:



A = Screw terminal


Switching positions:



Wiring diagrams:



Mounting cut-outs:



A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm