





LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D1	REVISED PER ECR-07-006494	28JUN07	HMR	GJ
			D2	REVISED PER ECO-09-024606	28OCT09	KK	AEG



- 1 SPECIFICATIONS:
MAGNET WIRE #34 - #18 AWG
.006"(0.16mm)-.040"(1.02mm)DIA COPPER.
- 2 POCKET RECOMMENDATION:
FOR POCKET DESIGN SEE #1601475
- 3 TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPECIFICATION
114-13166 FIGURE 12.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	—	—	—
	—	—	—
	—	—	—
OBSOLETE	PRE-TIN PLATE OVER COPPER UNDERPLATE	031-177-014	4-1601106-2
4 OBSOLETE	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-178-014	2-1601106-2
	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-177-014	1601106-2
	FINISH	REFERENCE PART NUMBER	TYCO PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .01 [0.25] 3 PLC ± .005 [0.13] 4 PLC ± — ± 2' ANGLES	PRODUCT SPEC 108-2085 APPLICATION SPEC 	NAME STANDARD RANGE WIRE TO .118 X .025 MULTI-BARB SIAMEZE TERMINAL
MATERIAL BRASS, 3/4 HARD	FINISH SEE TABLE	WEIGHT —	SIZE A2
		CAGE CODE 00779	DRAWING NO C-1601106
		CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 1 REV D2