







2198235
MOUNTED BELLY TO BELLY ON PCB
SCALE 3:1



- | REV. NO. | | DATE | | REVISIONS | |
|----------|----|------|-----|----------------------------|--|
| GP | 00 | P | LTR | DESCRIPTION | |
| | | A | | RELEASED PER ECO-12-013192 | |
| | | B | | RELEASED PER ECO-13-000564 | |
| | | B1 | | RELEASED PER ECO-13-014600 | |
| | | B2 | | RELEASED PER ECO-15-006578 | |

1	MATERIAL:	CAGE ASSEMBLY: 0.25mm THICK NICKEL SILVER ALLOY. HEATSINK CLIP: STAINLESS STEEL HEATSINK: ALUMINUM
2	FINISH:	EMI SPRINGS: MINIMUM OF 0.8um TIN PLATE OVER A MINIMUM OF 0.8um NICKEL UNDERPLATE. NON-PLATED EDGES PERMISSIBLE. HEATSINK CLIP: PASSIVATE HEATSINK: ELECTROLESS NICKEL
3.	MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.	
4	PADS AND VIAS CHASSIS GROUND.	
5.	INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OF ASME Y14.5M-1994.	
6	MINIMUM PC BOARD THICKNESS:	SINGLE SIDED = 1.50mm DOUBLE SIDED = 2.25mm
7	HOLE PATTERN REPEATS FOR EACH PORT. SPACING BETWEEN PORTS IS 14.25mm.	
8	DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.	
9	REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.	
10	REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.	
11.	CERTAIN MATING TRANSCEIVERS MAY REQUIRE ADDITIONAL PCB THICKNESS THAT WOULD BE DETERMINED BY THE CUSTOMER.	
12.	PRODUCT COMPLIES WITH SPECIFICATION SFF-8433 IMPROVED PLUGGABLE FORM FACTOR FOR SFP+ GANGED CAGES.	
13.	DIMENSION APPLIES PRIOR TO INSERTION OF SFP MODULE	





FIN TYPE	W/O INSULATING TAPE	22.5	NETWORKING, TALL	2198235-9
FIN TYPE	W/O INSULATING TAPE	18.1	NETWORKING, SHORT	2198235-8
FIN TYPE	W/O INSULATING TAPE	15.5	SAN	2198235-7
FIN TYPE	W/O INSULATING TAPE	13.2	PCI	2198235-6
PIN TYPE	W/ INSULATING TAPE	22.5	NETWORKING, TALL	2198235-5
PIN TYPE	W/O INSULATING TAPE	22.5	NETWORKING, TALL	2198235-4
PIN TYPE	W/O INSULATING TAPE	18.1	NETWORKING, SHORT	2198235-3
PIN TYPE	W/O INSULATING TAPE	15.5	SAN	2198235-2
PIN TYPE	W/O INSULATING TAPE	13.2	PCI	2198235-1
HEAT SINK	DESCRIPTION	A MAX	APPLICATION	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 15NOV2011 CHK M. SCHMITT 15NOV2011 APP'D M. SCHMITT 15NOV2011		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES $\pm 1^\circ$		NAME SFP+ ENHANCED 1X6 CAGE ASSEMBLY, PRESS FIT, EXTERNAL EM1 SPRINGS WITH HEATSINK	
		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SIZE CASE CODE DRAWING NO RESTRICTED TO A1 00779 C=2198235	
MATERIAL 		FINISH 		WEIGHT -	
Customer Drawing		SCALE 4:1		SHEET 1 of 7 REV A	




2198235
MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL



2198235
MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 15NOV2011	 TE Connectivity	
DIMENSIONS:		CHK M. SCHMITT 15NOV2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. SCHMITT 15NOV2011	NAME SFP+ ENHANCED 1X6 CAGE ASSEMBLY, PRESS FIT, EXTERNAL EMI SPRINGS WITH HEATSINK	
	0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1° FINISH	PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120	SIZE A100779	
MATERIAL		WEIGHT -	DRAWING NO. C=2198235	
Customer Drawing		SCALE 4:1		SHEET 3 OF 7
				REV B2



LOC		DIST		REVISIONS			
GP	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 15NOV2011 CHK M. SCHMITT 15NOV2011		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 ANGLES $\pm 1^\circ$		NAME SFP+ ENHANCED IXX6 GAGE ASSEMBLY, PRESS FIT, EXTERNAL EMI SPRINGS WITH HEATSINK	
		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SIZE A1	
MATERIAL 		FINISH WEIGHT -		DRAWING NO C=2198235	
		Customer Drawing		SCALE 4:1 SHEET 5 OF 7 REV B2	



RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
SINGLE SIDED APPLICATIONS
FOR WITH INSULATING TAPE PART 6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 15NOV2011 CHG M. SCHMITT 15NOV2011 APVD M. SCHMITT 15NOV2011		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 0.1		NAME SFP+ ENHANCED 1X6 CAGE ASSEMBLY, PRESS FIT, EXTERNAL EMI SPRINGS WITH HEATSINK	
		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SIZE A1	
MATERIAL FINISH		WEIGHT -		DRAWING NO C=2198235	
Customer Drawing		SCALE 4:1		SHEET 6 OF 7	
				REV B2	

