

Relays, Contactors & Switches > Relays > Mil-Aero Relays > TO-5/.100 Grid Relays



Contact Arrangement: **2 Form C, DPDT, 2 C/O**

Input Voltage: **2.6 VDC**

Coil Suppression Diode: **Without**

Contact Current Rating: **1 A**

Coil Voltage: **5 VDC**

Features

Product Type Features

| | |
|----------------|-------------------------------------|
| Enclosure Type | Hermetically Sealed |
| Relay Type | Military/Aerospace High Performance |
| Coil Latching | Without |
| Product Type | Relay |

Electrical Characteristics

| | |
|---------------------------------|---------------------------|
| Coil Magnetic System | Non-Polarized, Monostable |
| Vibration | 30G's, 10 – 3000Hz |
| Actuating System | DC |
| Shock | 75G's, 6ms |
| Coil Power Measurement | Milliwatts |
| Input Voltage | 2.6 VDC |
| Coil Suppression Diode | Without |
| Coil Voltage | 5 VDC |
| Coil Resistance | 100 Ω |
| Coil Power Rating (DC) | 250 mW |
| Contact Switching Voltage (Max) | 28 |

Contact Features

| | |
|-----------------------|-----------------|
| Contact Current Class | Low Level – 1 A |
| Pin Configuration | Ground Pin |

| | |
|------------------------|-----------------------|
| Contact Arrangement | 2 Form C, DPDT, 2 C/O |
| Contact Current Rating | 1 A |

Termination Features

| | |
|------------------|---------|
| Termination Type | PC Pins |
|------------------|---------|

Mechanical Attachment

| | |
|---------------|-----------------------|
| Mounting Type | Printed Circuit Board |
|---------------|-----------------------|

Usage Conditions

| | |
|-----------------------------|--------------|
| Operating Temperature Range | -65 – 125 °C |
|-----------------------------|--------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197) |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not lead free process capable |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1617036-6
HFW4A1201D00 = HFW
4A RELAY

Also in the Series | CII MW



High Frequency Relays(11)



TO-5/.100 Grid Relays(11)

Customers Also Bought



TE Part #1052982-1
2054 1231 02



TE Part #226782-1
ARINC SIZE 15 SOCKET



TE Part #1622239-1
LR0204 1% 43R



TE Part #1051869-1
2032 5026 02



TE Part #226781-1
ARINC SIZE 15 SOCKET



TE Part #1625813-2
3632 10000UH 15% FIO



TE Part #1623952-1
SC10-10-0531-10 33UH
AMMO 1000



TE Part #1623957-2
SC10-10-0533-10 47UH
AMMO 1000



TE Part #1623976-1
SC10-10-0511-10 0.68UH
AMMO 1000

Documents

Datasheets & Catalog Pages

[5-1773450-5_sec2_MW3](#)

English