




MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FED. MFR. CODE 91929SWITCH - TOGGLE
(MAGNETIC HOLD-IN)CATALOG LISTING
26ET55-2

NOTES

- 1 - EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIAL OR ARE SUITABLY PROTECTED TO PREVENT CORROSION. ENCLOSURE FINISHED WITH BLUE EPOXY BASED ENAMEL COLOR NO. 25184 PER FEDERAL STANDARD 595
- 2 - SWITCH SEALED PER MIL-S-5594
- 3 - HOLD IN VOLTAGE: THE MINIMUM SPECIFIED VOLTAGE AT WHICH THE LEVER WILL REMAIN ACTUATED. HOLD IN MAY OCCUR AT A LOWER VALUE.
DROP OUT VOLTAGE: THE VOLTAGE RANGE IN WHICH THE LEVER WILL BE RELEASED
- 4 - CIRCUITS CAN BE TRANSFERRED MANUALLY. ENERGIZING THE COIL WILL NOT CAUSE TRANSFER OF CIRCUITS
- 5 - CIRCUIT IDENTIFICATION IS SHOWN ON SWITCH
- 6 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 7 - HARDWARE MAYBE FURNISHED UNASSEMBLED PER MIL-S-5594

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS 3

SOLENOID RATING AT 20° C	
STEADY STATE LIMITS-----	20-29 VDC
HOLD IN 3-----	15 VDC
DROP OUT 3-----	0-15 VDC
OVERRIDE FORCE AT 29 VDC----	10 LB MAX
OPERATING FORCE-----	7 LB MAX
COIL RESISTANCE-----	220 OHM MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (2)

VOLTAGE	RATING IN AMPERES			
	SEA LEVEL		65,000 FT	
28 VOLTS DC	RES	IND	MOTOR	
	4	2.5	4	

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE (.0)	±.030
TWO PLACE (.00)	±.015
THREE PLACE (.000)	±.005
ANGLES	±

WEIGHT 7.5 OZ MAX

M 26ET55-2

DRAWING
NUMBERISSUE
X 5

REVISIONS

A	CORR - CO 35817
B	GLH 28 JUL 75
C	CO 50162
D	WJM 6 OCT 81
E	CO 53401
F	J A P 17 MAR 84
G	0041615
H	MBH 14 JUL 08

FO-50376-003