


F I E I D C I B I A



Technical specification:

Technische Daten:

Dielectric withstanding voltage/ Spannungsfestigkeit:	1000 V, 50 Hz 1 min.
Current rating/ Strombelastbarkeit:	Signal contact/ 7,5 A (UL) Signalkontakt: 5 A (CSA,VDE)
Insulation resistance/ Isolationswiderstand:	$\geq 5 \text{ G}\Omega$
Temperature range/ Temperaturbereich:	- 55 °C ... + 125 °C
Mating cycles/ Steckzyklen:	Quality class 3 = 50 Gütestufe 3

Materials/





Werkstoffe:

Contact/ Kontakt:	Cu alloy, Au over Ni
Insulator/ Isolierkörper:	PBT GF UL 94 V-0, green/grün
Shell/ Gehäuse:	Steel, Sn over Ni
Threaded spacer clip/ Abstandsbolzen Clip:	Cu alloy, Sn over Ni
Collar/ Scheibe:	Cu alloy, Sn over Ni

Installation specification/


Montagedaten:

Recommended torque	max. 6 in.LB/
Value for thread/ empfohlenes Drehmoment für Gewinde:	max. 67 Ncm
PCB clip for hole diameter/ PCB Clip für Lochdurchmesser:	$\varnothing 3,1 \text{ mm}$
PCB thickness/ Leiterplatten Dicke:	1,6 mm



Part no. / Part marked Art.-Nr. / Bedruckung:	Contact plating/ Kontakt Veredelung:
3017W2SAR99E20X	Signal contact Signalkontakt: gold flash over nickel Gold über Nickel
	No Contacts on pos. A1 - A2 keine Hochstromkontakte an Pos. A1 - A2

Index: Original	Scale/Maßstab: 2:1	dwg no / Z.-nr.: 13K1A5380	DIN-A3
Status: InBearbeitung			1 / 1
RoHS compliant/ konform			



D-SUB Combination Female 17W2S
with threaded spacer clip
D-SUB Combination Buchsenleiste 17W2S
mit Abstandsbolzen-Clip