

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

-

F4

8-188431-6 ACTIVATED

20AUG2014

NV

JK

## NOTES:

- 1 PACKAGING ACCORDING EIA-481/ DIN IEC 286
- 2 QUANTITY PER REEL 1200 PCS. REEL DIA. 380 MM
- 3 PN 9-188431-0 (20 POSITIONS) AS DRAWN.
- 4 3.0 - 5.0  $\mu$ m TIN OVER 0.5  $\mu$ m NICKEL PLATING.
- 5 PICK & PLACE AREA.

PACKAGING/REELING DIRECTION

USER DIRECTION OF FEED

see detail A

DETAIL A  
SCALE 1:1

SECTION A-A

RECOMMENDED PC- BOARD PAD LAYOUT

SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

|        |   |     |
|--------|---|-----|
| 0 PLC  | ± | -   |
| 1 PLC  | ± | 0.2 |
| 2 PLC  | ± | -   |
| 3 PLC  | ± | -   |
| 4 PLC  | ± | -   |
| ANGLES | ± | -   |
| FINISH |   |     |

MATERIAL

SEE TABLE

SEE TABLE

DWN 25/09/00

M.Gosselink

CHK

M.Gosselink

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318

WEIGHT

-

CUSTOMER DRAWING

**TE**

TE Connectivity

NAME  
MICRO MATCH, FEMALE BOTTOM ENTRY  
SMD INBOARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

C-

188431

SCALE 4:1

SHEET 1 OF 1

REV F4