


10/100/1000 BASE-T SINGLE & DUAL TRANSFORMER MODULE



Ruggedized



- ⦿ Compliant with IEEE 802.ab for 1000Base-T
- ⦿ 350µH OCL with 8mA bias at extended temperatures
- ⦿ Two Operating & Storage Temperature versions available:
 - Standard: -40°C to +85°C
 - Extended: -55°C to +125°C
- ⦿ Peak Reflow Temperature: 245°C (for RoHS versions)
- ⦿ Moisture Sensitivity Level: 3

Electrical Specifications @ 25°C

Part Number	Insertion Loss (dB MAX)				Return Loss (dB MIN)				Crosstalk (dB MIN)			CM to CM Rejection (dB MIN)			DM to CM Rejection (dB MIN)			HiPot (Vrms)
	0.10 MHz	30 MHz	60 MHz	100 MHz	30 MHz	60 MHz	80 MHz	100 MHz	30 MHz	60 MHz	100 MHz	30 MHz	60 MHz	100 MHz	30 MHz	60 MHz	100 MHz	
1000B-5009F	1.4	1.4	1.4	1.4	18	12	10	8	43	37	31	30	25	18	40	35	30	1500
1000B-5009FX	1.4	1.4	1.4	1.4	18	12	10	8	43	37	31	30	25	18	40	35	30	1500
1000B-5012F	1.2	1.2	1.2	1.2	18	12	10	8	43	37	33	40	35	30	43	37	30	1500
1000B-5012FX	1.2	1.2	1.2	1.2	18	12	10	8	43	37	33	40	35	30	43	37	30	1500
1000B-5014F	1.4	1.4	1.4	1.4	16	12	10	8	43	37	33	33	30	28	43	37	30	1500
1000B-5014FX	1.4	1.4	1.4	1.4	16	12	10	8	43	37	33	33	30	28	43	37	30	1500
1000B-5016F	1.2	1.2	1.2	1.2	18	12	12	10	43	37	31	30	23	17	40	35	30	1500

NOTES:



1. Add suffix "X" for extended temperature version; i.e. 1000B-5009F becomes **1000B-5009FX**. (*1000B-5016F does not offer an extended temperature version)
2. Add suffix "NL" for RoHS compliant version; i.e. 1000B-1012F becomes **1000B-1012FNL**. NL parts have 100% SN Lead Finish (MSL:4).
3. For Tape & Reel packaging, add "T" suffix at the end of the part number: i.e. **1000B-5014FT**.

Mechanicals

Electrical Schematics

1000B-5009F/X

Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]




Ruggedized




Electrical Schematics

Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]



Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]



Electrical Schematics

PORT 1

CHANNEL 1

(TCT1) 1
(TD1+) 2
(TD1-) 3

48 (CMT1)
47 (MX1+)
46 (MX1-)

CHANNEL 2

(TCT2) 4
(TD2+) 5
(TD2-) 6

45 (CMT2)
44 (MX2+)
43 (MX2-)

CHANNEL 3

(TCT3) 7
(TD3+) 8
(TD3-) 9

42 (CMT3)
41 (MX3+)
40 (MX3-)

CHANNEL 4

(TCT4) 10
(TD4+) 11
(TD4-) 12

39 (CMT4)
38 (MX4+)
37 (MX4-)

PORT 2

CHANNEL 1

(TC15) 13
(TD5+) 14
(TD5-) 15

36 (CMT5)
35 (MX5+)
34 (MX5-)

CHANNEL 2

(TC16) 16
(TD6+) 17
(TD6-) 18

33 (CMT6)
32 (MX6+)
31 (MX6-)

CHANNEL 3

(TC17) 19
(TD7+) 20
(TD7-) 21

30 (CMT7)
29 (MX7+)
28 (MX7-)

CHANNEL 4

(TC18) 22
(TD8+) 23
(TD8-) 24

27 (CMT8)
26 (MX8+)
25 (MX8-)

LEGEND

Channel	Input	Output
CHIP	Td	Mx
	Td	Mx
	Td	Mx
	Td	Mx
SIDE	Td	Mx
	Td	Mx
	Td	Mx
	Td	Mx

All channels are in phase between input and output



iNRCORE, LLC
311 Sinclair Road, Bristol, PA 19007-6812 USA
Tel: +1.215.781.6400 Fax: +1.215.781.6430

www.iNRCORE.com

M160.G (11/21)


Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. INRCORE, LLC. All rights reserved.

Ruggedized



Electrical Schematics

Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]



The graph illustrates the temperature profile of a sample during a DSC scan. The y-axis represents Temperature, and the x-axis represents Time. The curve begins at 25°C, rises through a preheat area, reaches a peak at T_p , and then falls. Key parameters labeled include T_{smax} , T_c (5°C below T_p), T_l , and time intervals t_s , t_p , and t_l . Ramp rates are specified as 3°C/s up and 6°C/s down.

T_{SMIN} (°C)	T_{SMAX} (°C)	T_L (°C)	T_P (°C MAX)	t_S (s)	t_L (s)	t_P (s MAX)	Ramp-up rate (T_L to T_P)	Ramp-down rate (T_P to T_L)	Time 25°C to peak temperature (s MAX)
100	150	183	235	60 - 120	60 - 150	20	3°C/s MAX	6°C/s MAX	360

1. All temperatures measured on the package leads.
2. Maximum times of reflow cycle: 2

www.iNRCORE.com

M160.G (11/21)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020, INRCORE, LLC. All rights reserved.

