


REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	D3	REVISED PER ECO-15-011938	21AUG2015	NK	MM	
	E	REVISED PER ECR-17-001423	03FEB2017	RS	MM	



- 1   SHALL BE INTERSECTION OF THE POST
AND THE HOUSING.
- 2  THE NOTED DIMENSIONS APPLY AT THE INTERSECTION
OF THE POST AND THE HOUSING.
- 3  0.00254—0.00508 [.000100—.000200] MATTE TIN—LEAD
OVER 0.00127 [.000050] MIN NICKEL ENTIRE POST.
- 4  HOUSING : LCP, COLOR—BLACK.
POST : PHOSPHOR BRONZE.
PICK AND PLACE CAP: PPA, COLOR—BLACK.
- 5 PACKAGED IN TAPE AND REEL PER EIA—481 SPECIFICATIONS.
SEE TABLE FOR WIDTHS.
- 6  PRELIMINARY PART NUMBER — NOT RELEASED FOR PRODUCTION.
- 7  0.00254—0.00508 [.000100—.000200] MATTE TIN
OVER 0.00127 [.000050] MIN NICKEL ENTIRE POST.

		56 mm	35.56 [1.400]	14	37.69 [1.484]	15	6-147548-3
		56 mm	33.02 [1.300]	13	35.15 [1.384]	14	6-147548-2
		56 mm	30.48 [1.200]	12	32.61 [1.284]	13	6-147548-1
		56 mm	27.94 [1.100]	11	30.07 [1.184]	12	6-147548-0
		56 mm	25.40 [1.000]	10	27.53 [1.084]	11	5-147548-9
		56 mm	22.86 [.900]	9	24.99 [.984]	10	5-147548-8
		56 mm	20.32 [.800]	8	22.45 [.884]	9	5-147548-7
		44 mm	17.78 [.700]	7	19.91 [.784]	8	5-147548-6
		44 mm	15.24 [.600]	6	17.33 [.684]	7	5-147548-5
		24 mm	10.16 [.400]	4	12.29 [.484]	5	5-147548-4
		32 mm	12.70 [.500]	5	14.83 [.584]	6	5-147548-3
		24 mm	7.62 [.300]	3	9.75 [.384]	4	5-147548-2
		24 mm	5.08 [.200]	2	7.21 [.284]	3	5-147548-1
		56 mm	20.32 [.800]	8	22.45 [.884]	9	147548-4
		32 mm	12.70 [.500]	5	14.83 [.584]	6	147548-3
		24 mm	7.62 [.300]	3	9.75 [.384]	4	147548-2
		24 mm	5.08 [.200]	2	7.21 [.284]	3	147548-1
	PLATING	TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER

RECOMMENDE PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER		20SEP00		 TE Connectivity			
		CHK J. GESFORD		20SEP00					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. GESFORD		20SEP00		NAME	
		0 PLC ± -		PRODUCT SPEC		SURFACE MOUNT HDR ASSY, MOD II, B/A VERT , S/R .100CL, .025 SQ. POST, WITH PICK AND PLACE CAP			
		1 PLC ± -		—					
		2 PLC ± -		APPLICATION SPEC					
		3 PLC ± 0.13 [.005]		—					
		4 PLC ± -							
		ANGLES ± -		WEIGHT					
MATERIAL		FINISH		—		SIZE		CAGE CODE	
		SEE TABLE				A2		00779	
				CUSTOMER DRAWING		DRAWING NO		RESTRICTED TO	
						A2		00779	
						C-147548		—	
						SCALE		SHEET	
						4:1		1 OF 1	
								REV	
								F	