


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	HOUSING COLOR	DIMENSIONS in. [mm]					
			L ± .02 [0.6]	W ± .02 [0.6]	H ± .02 [0.6]	C ± .04 [1.1]	D ± .006 [0.15]	T ± .01 [0.3]
EQSP18	#22-18 [0.5-0.75]	RED	.79 [20.0]	.46 [11.8]	.48 [12.3]	.14 [3.5]	.017 [.43]	.031 [.8]
EQSP14*	#18-14 [0.75-2.5]	BLUE	.77 [19.6]	.47 [12.0]	.48 [12.3]	.14 [3.5]	.028 [.70]	.031 [.8]
EQSP10	#12-10 [4.0-6.0]	YELLOW	.81 [20.5]	.60 [15.2]	.66 [16.7]	.24 [6.0]	.047 [1.20]	.035 [.9]

*NOT UL LISTED

NOTES:

- USED FOR:
 - EQSP18 & EQSP14 SOLID AND STRANDED COPPER WIRE
 - EQSP10 STRANDED COPPER WIRE ONLY
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600 V. MAX VOLTAGE RATING
- MATERIAL:
 - STAMPING: BRASS, TIN PLATED
 - HOUSING: POLYPROPYLENE
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
20U0
E52164

TITLE			
STRONGHOLD QUICK SPLICE CONNECTOR INSULATION DISPLACEMENT, #22-10 AWG			
CUSTOMER DRAWING			
ITEM REVISION NAME		00123SSH/00	
DATASET FILE NAME		00123SSH/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xx ± .01 [.25]		.xxx ± .005 [.127] ANGLES ± 5°	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWING NUMBER:		00123SSH-DC	
DRAWN BY	DATE	CHK	SCALE
JHNU	-	-	N.T.S.
SHT 1 OF 1			SIZE A

00	2/18	JHNU	TMR	RGB	DRAWING RELEASED	00123SS
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN