




NOTES

NOTES

1. MATERIAL: SEE TABLE;
2. COLOR: SEE TABLE;
3. APPLICABLE TERMINALS: SEE TABLE;
4. APPLICABLE SEALS: SEE TABLE;
5. FOR GENERAL GEOMETRICAL TOLERANCE SEE TABLE (ECCENTRICITY);
6. HANDLING MANUAL: YES-15-989E;
7. PRODUCT STANDARD: YPES-11-98-148E;
8. THE MATERIALS USED IN THIS PRODUCT ARE IN CONFORMANCE WITH THE REQUIREMENTS OF EU EN 2000/53/EC DIRECTIVE AND

YAZAKI PART No.	No.	PART NAME	PART NUMBER	MATERIAL	d Δ	A Δ	INSULATION DIAMETER	WIRE SIZE	COLOUR	APPLICABLE TERMINALS
7158-3673-90	1	RUBBER STOPPER	7172-0169-40	PBT-GF15	6.5	8.20	7.3 - 8.3 mm	16 mm ²	LIGHT GREY	7116-5625-02
	2	SEAL RUBBER		SILICON RUBBER					TURQUOISE	7116-5625-06
7158-3672-50	1	RUBBER STOPPER	7172-0169-40	PBT-GF15	5.2	8.20	6.15 - 7.3 mm Δ	16 mm ²	LIGHT GREY	7114-5623-02
	2	SEAL RUBBER		SILICON RUBBER					LIGHT PINK	7114-5623-06
7158-3713-70	1	RUBBER STOPPER	7172-0169-40	PBT-GF15	4.3	8.20	5.3 - 6.5 mm Δ	10 mm ² Δ	LIGHT GREY	7116-5625-02
	2	SEAL RUBBER		SILICON RUBBER					YELLOW	7116-5626-06
7172-5643-50	1	RUBBER STOPPER	7172-0169-40	PBT-GF15	3.2	7.00	4.6 - 5.0 mm	8 mm ²	LIGHT GREY	7114-5623-02
	2	SEAL RUBBER		SILICON RUBBER					RED	7114-5624-02
7172-5184	1	RUBBER STOPPER	7172-0169-40	PBT-GF15	1.85	7.00	3.4 - 4.3 mm	4 - 6 mm ²	LIGHT GREY	7116-3250
	2	SEAL RUBBER		SILICON RUBBER					NATURAL	7114-3250

ISOMETRIC VIEW

(SCALE: 1:1)



A

Δ	15.02.2017.	ADDED NEW PART	I.J.	Y17-0128
Δ	05.07.2016	UPDATED TABLE	B.F.	Y16-0437
Δ	16.06.2014	UPDATED TABLE	B.F.	Y14-0318
Δ	19.11.2013	ADD DIMENSION	J.J.	Y13-0645
Δ	20.03.2013	ADDED NEW PART	J.J.	Y13-0738
Δ	27.06.2007	UPDATED TABLE	J.J.	C07-D723
Δ	12.06.2007	UPDATED TABLE	J.J.	C07-0705
Δ	30.05.2007	ADDED NEW PART	J.J.	C07-D5676
Δ	24.01.2007	NEW	J.J.	C07-D522
ET	DATE	REVISION RECORD	NO.	CHKO

CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG. NO.	MAT'L SPEC.	SEE TABLE	TREAT. & FIN.	ISSUE MARK
OFFICE	YEL-K	TRIAL PART NO	NAME	9.5 YPT WP CONNECTOR	Δ	
VENDOR	X30658-D756 ETC.			SINGLE WIRE SEAL		
GENERAL TOLERANCE						
10MAX	50MAX	100MAX	250MAX	2500/R	ANGLE	ECCENT
A ±0.15	±0.2	±0.3	±0.5	±0.75	± 30°	0.1
B ±0.2	±0.3	±0.55	±0.95	±1.4	± 30°	0.1
C ±0.3	±0.5	±0.8	±1.4	±2	± 30°	0.15
SPECIFIED						
MASS					Δ	34 - 1.94 g
						
DATE	16.02.2017	16.02.2017	10.10.2006	11.05.2017.		